

OptiSnap® Single-Mode Field-Installable Connector Toolkits

Features and Benefits

Minimal setup and teardown time

Allows installers to get in and out of installation sites quickly; no work surface needed

Fastest termination, highest installation yields and no consumables

Lowest installation costs

Go/no-go feedback technology

Immediate indication of successful termination

Convenient carrying case

One tool kit for LC, SC and ST® Compatible Connector types UPC and APC

With proven field-installable connector technology, fiber terminations using the OptiSnap® connector system are fast, easy and reliable. Corning high-precision mechanical splice technology enables fiber optic networks to be installed quickly and cost effectively.

The Corning go/no-go feedback signal allows the installer to verify that the installation is performed right the first time, every time. Insert the fiber, activate the cam and watch the pass/fail light illuminate, instilling confidence in every connector installed.

The single-mode OptiSnap Connector is available in an ultra physical contact (UPC) polish or an angled physical contact (APC) polish (SC only), offering you a higher grade of performance for your field terminations. With fast installation time and low insertion loss, the OptiSnap Connector system provides a good alternative to fusion splicing. Installation is as easy as strip, clean, cleave, cam and crimp.



OptiSnap® Single-Mode Field-Installable Connector Toolkits

Ordering Information

| Single-mode | | |
|--------------------|---|--------------------|
| Part Number | Description | Units per Delivery |
| TKT-OPTISNAP-CF | OptiSnap® Connector Installation Tool Kit with flat cleaver includes installation tool, all required fiber preparation and cleaning supplies in a gray case | 1/1 |
| FBC-009 | High-Performance Precision Flat Cleaver with diamond blade and fiber handlers | 1/1 |
| FBC-14-15-16-BLADE | Replacement diamond blade for the high-performance flat cleaver, for FBC-007 and FBC-015 flat cleavers | 1/1 |
| VFL-A125 | LC 1.25 mm VFL Ferrule Adapter | 1/1 |
| VFL-A250 | Standard Ferrule 2.5 mm VFL Adapter | 1/1 |
| VFL-AKIT | LC 1.25 mm VFL Ferrule Adapter Kit | 1/1 |
| CLEAN-STICKS-125 | 1.5 mm Ferrule Cleaning Sticks | 10/1 |
| CLEAN-STICKS-250 | SC and ST® compatible 2.5 mm Ferrule Cleaning Sticks | 10/1 |
| FCC-CLEANER-FIBER | Bottle of Corning Fiber Cleaning Fluid | 1/1 |
| FCC-WIPES | Lint-free Cleaning Wipes, canister of 90 | 90/1 |

Note: Individual OptiSnap connector installation tools are available for order. Please contact a Corning Customer Care Representative.



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC 28216 United States
 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks.
 Corning Optical Communications is ISO 9001 certified. © 2020 Corning Optical Communications. All rights reserved.