CORNING

Standard Recommended Procedure
SRP-205-308
Issue 6, February 2015

Add-A-Line Installation Instructions for CAC® 3000, CAC 900, MLP 600 & KEPTEL 2100 Products

CAC 3000



Parts Required



Snapjack with Jack Module



Bridge



Protector



CAC 3000

1. Insert snapjack with the gray jack module.
2. Remove unused tab from protector by moving it back and forth with pliers until it breaks off.
3. Install protector, as required.
4. Cut terminals from snapjack wires.
5. Connect snapjack wires to back of protector as shown. Verify wires are fully inserted.

CAC 900



Parts Required



Snapjack



Bridge

Protector

CAC 900

1. Remove the snapjack from the jack module which is provided in the kit.
2. Pry CAC 900 module out of the base using a large screwdriver by twisting the screwdriver counterclockwise.
3. Insert the snap jack into the CAC 900 module that you removed from the base, and press the module back into the base.
4. Remove unused tab from protector by moving it back and forth with pliers until it breaks off.
5. Install the protector.
6. Cut terminals from snapjack wires.
7. Connect snapjack wires to back of protector as shown. Verify wires are fully inserted.

MLP 600 (Plastic)



Parts Required



Snapjack



Bridge



Protector



MLP 600

1. Insert snapjack into base.
2. Remove unused tab from protector by moving it back and forth with pliers until it breaks off.
3. Install protector.
4. Cut terminals from snapjack wires.
5. Connect snapjack wires to back of protector as shown. Verify wires are fully inserted.
6. Install customer termination bridge by snapping into base.

KEPTEL 2100



Parts Required



Snapjack



Bridge



Bridge Adapter

Jack Adapter



Protector



Bridge Assembly

KEPTEL 2100

1. Insert snapjack into black jack adapter.
2. Then insert adapter into base.
3. Remove unused tab from protector by moving it back and forth with pliers until it breaks off.
4. Install protector.
5. Cut terminals from snapjack wires.
6. Connect snapjack wires to back of protector as shown. Verify wires are fully inserted.
7. Install customer termination bridge by snapping into black bridge adapter.
8. Install adapter into base, using the two long screws provided.

Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

Corning Optical Communiations reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 1994, 1995, 1998, 2003, 2009, 2015 Corning Optical Communications. All rights reserved.