

Certificate

No. z3695a-14-E

Customer:

Corning Cable Systems GmbH & Co. KG
Austrasse 101
96465 Neustadt/Coburg, Germany

Class E_A

Test sample(s):

Data Cable:

Corning FutureCom S/FTP 550/23s, 6-way, LS0H-1 Cable: twisted pair, foilshielded pair (PIMF) and braid shield, single cable spec. up to 550MHz, AWG 23, 6xS/FTP 550/23s with common foil

Part no.: CCXEDR-D0247-C002-L7

Patchcord:

Corning FutureCom Cat.6A Patchcord S/FTP flex/26, 2xRJ45, 4P

Part no.: CCAGB-G1002-A020-C0

Connector:

S500 module, Cat.6A, 1xRJ45; S500 keystone, Cat.6A, 1xRJ45;

S500fx module, Cat.6A, 1xRJ45; S500fx keystone, Cat.6A, 1xRJ45

Part no.: CAXASM-00104-C001; CAXBSM-00104-C001;

CAXASM-00104-C002; CAXBSM-00104-C002

Applied standard(s):

ISO/IEC 11801 Ed.2.2 (2011-06)

Result(s):

The sample meets the limits of the specified standards and regulations with respect to the parameters indicated above.

2 Connector Channel (95m), Copper, Class E_A

GHMT Type Approval

The test results which were determined in the course of the measurement refer to the submitted specimen. Any future technical modifications of the verified products are subject to the responsibility of the manufacturer.

This Certificate refers to the comprehensive test report no. **P3695a-14-E** and shall only be applicable in conjunction with the test report. This certificate is valid 24 months after date of issue.

Bexbach, 09. September 2014



Dirk Wilhelm, engineer
(Chairman of the Managing Board)



GHMT AG

In der Kolling 13
66450 Bexbach / Germany

P0 box 11 16
66442 Bexbach / Germany

T: +49 6826 92 28-0
F: +49 6826 92 28-290

info@ghmt.de
www.ghmt.de

RELIABILITY IN TOTAL
REQUIRES ACCURACY IN DETAIL.