

Centrix™ Splice Housing, Pigtailed

4U, 12 Cassettes each with 24 SC APC adapters & SM Pigtails, 250 μm standard SM Pigtails, total of 288 F

CORNING

A Centrix™ System 4U housing holds 12 cassettes. Housings can be ordered with cassettes for on-frame splicing. At the foundation of the Centrix System is a single, modular cassette that can be tailored to include a variety of optical devices (splitter, WDM, etc). The modular cassette provides flexibility and functionality within a single frame without sacrificing density. Each cassette contains up to either 24 SC or 36 LC connector adapters. Easy port access is possible due to a sliding cassette with drop-down handle.

Features

- Loaded housing with 288 SC/APC Ports ready for splicing
- Faster system setup and reduced packaging material
- 300mm depth for installation in telco cabinets
- Easy port access and identification
- Integrated patch cord guide supports patch management
- Front and top labeling for easy identification
- Fiber identification with VFL (visual fault location) in the adapter
- Captive covers on both sides of the cassette
- Multiple tube entry from the rear or both sides on the cassette
- Bare fiber and tube slack storage up to 2m by design



Temperature Range	
Operation	-40 °C to 70 °C

Design - Hardware	
Fiber Type	SM
Number of Ports	288
Connector Type	SC APC
Pigtail Type	900 μm
Height Unit	4U

Centrix™ Splice Housing, Pigtailed

4U, 12 Cassettes each with 24 SC APC adapters & SM Pigtails, 250 µm standard SM Pigtails, total of 288 F



Mechanical Characteristics

Dimensions (H x W x D)	178 mm x 305 mm x 521 mm (7.0 in x 12.0 in x 20.51 in)
Weight	10.4 kg (23 lb)

Ordering Information

Part Number	CX4U8P24-6C-2RH000
Product Description	Centrix™ Splice Housing, 4U, 12 Cassettes each with 24 SC APC adapters & SM Pigtails, 250 µm standard SM Pigtails, total of 288 F
EAN Code	4056418145709

Shipping Information

Box Dimensions	520 mm x 265 mm x 500 mm (20.47 in x 10.43 in x 19.69 in)
Shipping Weight	15 kg (33.07 lb)
Units per Delivery	1/1



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2018 Corning Optical Communications. All rights reserved.