

Centrix™ Splice Housing, Pigtailed

4U, 12 Cassettes each with 24 SC APC adapters & SM Pigtails, 250 μm standard SM Pigtails, total of 288 F

CORNING

A Centrix™ System 4U housing holds 12 cassettes. Housings can be ordered with cassettes for on-frame splicing. At the foundation of the Centrix System is a single, modular cassette that can be tailored to include a variety of optical devices (splitter, WDM, etc). The modular cassette provides flexibility and functionality within a single frame without sacrificing density. Each cassette contains up to either 24 SC or 36 LC connector adapters. Easy port access is possible due to a sliding cassette with drop-down handle.



Temperature Range

Operation	-40 °C to 70 °C
-----------	-----------------

Design - Hardware

Fiber Type	SM
Number of Ports	288
Connector Type	SC APC
Pigtail Type	900 μm
Height Unit	4U

Mechanical Characteristics

Dimensions (HxWxD)	17.8 cm x 52.1 cm x 30.5 cm (7.0 in x 15.0 in x 10.5 in)
Weight	10.4 kg (23 lb)

Centrix™ Splice Housing, Pigtailed

4U, 12 Cassettes each with 24 SC APC adapters & SM Pigtails, 250 µm standard SM Pigtails, total of 288 F



Ordering Information

Part Number	CX4U8P24-6C-2RH000
Product Description	Centrix™ Splice Housing, 4U, 12 Cassettes each with 24 SC APC adapters & SM Pigtails, 250 µm standard SM Pigtails, total of 288 F
EAN Code	4056418145709

Shipping Information

Dimensions (HxWxD)	28.2 cm x 55.9 cm x 42.2 cm (11.12 in x 16.625 in x 16.625 in)
Shipping Weight	11.8 kg (26 lb)
Units per Delivery	1/1



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2017 Corning Optical Communications. All rights reserved.