

# Zipcord Riser Cables, 2-Fibers

CORNING

## Features and Benefits

### Meets NEC® requirements

Meets burn test criteria

### All-dielectric strength member

Mechanical durability


## Standards

Approvals and Listings      National Electrical Code®  
(NEC®) OFNR, CSA FT-4,  
ICEA S-83-596


Flame Resistance              UL-1666 (for riser and ge-  
neral building applications)

Corning zipcord cables are designed for interconnect applications. Two 900 µm buffered fibers are surrounded by aramid yarn strength members and a flame-retardant jacket. This cable design offers mechanical durability and flame resistance that meet the requirements of the National Electrical Code® (NEC®) Article 770.

*This cable is available in 12 different jacket colors – blue, orange, green, brown, slate, white, red, black, yellow, violet, rose and aqua. The colored jacket allows for easy visual identification of the cables. The standard jacket color will be determined by the dominant fiber type in the cable and will use the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.*



Zipcord Riser Cables, 2-Fibers  
| Photo PIM2495




Zipcord Riser Cables, 2-Fibers  
| Photo PIM2495


CORNING

# Zipcord Riser Cables, 2-Fibers

CORNING



Zipcord Riser Cables, 2-Fibers  
| Photo PIM2495



Zipcord Riser Cables, 2-Fibers  
| Photo PIM2495

## Specifications

### Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Operation	0 °C to 70 °C (32 °F to 158 °F)
Installation	0 °C to 60 °C (32 °F to 140 °F)

\* Note: Corning recommends storing cable in a proper temperature environment prior to installation to allow the cable temperature to meet installation temperature range specifications for best installation results.

### Mechanical Characteristics Cable

Max. Tensile Strength, Short-Term	220 N (50 lbf)
Max. Tensile Strength, Long-Term	100 N (22 lbf)

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Weight	Product Type
2	1.6 mm x 3.55 mm (0.06 in x 0.13 in)	50 mm (2 in)	8 mm (0.3 in)	5 kg/km (3.5 lb/1000 ft)	Interconnect
2	2.0 mm x 4.45 mm (0.08 in x 0.18 in)	50 mm (2 in)	10 mm (0.4 in)	7.4 kg/km (5.2 lb/1000 ft)	Interconnect
2	2.8 mm x 5.65 mm (0.11 in x 0.22 in)	50 mm (2 in)	25 mm (1.0 in)	14.6 kg/km (10 lb/1000 ft)	Interconnect

\* Installed single-mode minimum bend radius of 20 mm is acceptable with a length no longer than 1 m subjected to the bend.

CORNING

# Zipcord Riser Cables, 2-Fibers

CORNING

## Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

## Transmission Performance

Multimode					
Fiber Core Diameter (µm)	62.5	50	50	50	50
Fiber Category	OM1	OM2	OM3	OM4	OM4 Extended Distance
Fiber Code	K	T	T	T	T
Performance Option Code	30	31	80	90	91
Wavelengths (nm)	850/1300	850/1300	850/1300	850/1300	850/1300
Maximum Attenuation (dB/km)	3.4/1.0	2.8/1.0	2.8/1.0	2.8/1.0	2.8/1.0
Serial 1 Gigabit Ethernet (m)	300/550	750/600	1000/600	1000/600	1100/600
Serial 10 Gigabit Ethernet (m)	33/-	150/-	300/-	550/-	600/-
Min. Overfilled Launch (OFL) Bandwidth (MHz*km)	200/500	700/500	1500/500	3500/500	3500/500
Minimum Effective Modal Bandwidth (EMB) (MHz*km)	220/-	950/-	2000/-	4700/-	5350/-

\* Assumes 1.0 dB maximum total connector/splice loss.

\* Assumes 0.7 dB maximum total connector/splice loss.

\* Meets 0.75 ns optical skew when used in all Corning Plug and Play™/EDGE™ systems solutions.

\* ITU-T G.652 D compliant.

Notes: 1) Improved attenuation and bandwidth options available.

2) Bend-insensitive single-mode fibers available on request.

3) Contact a Corning Customer Care Representative for additional information.

4) 50 µm multimode fiber macrobend loss ≤ 0.2 dB at 850 nm for two turns around 7.5 mm radius mandrel.

## Single-mode


Fiber Name	SMF-28e® fiber	ClearCurve® LBL
Fiber Category	G.652.D	G.657.A2/G.657.B2 (OS2)
Fiber Code	E	J
Performance Option Code	31	31
Wavelengths (nm)	1310/1383/1550	1310/1383/1550
Maximum Attenuation (dB/km)	0.65/0.65/0.5	0.65/0.65/0.5

CORNING

# Zipcord Riser Cables, 2-Fibers

CORNING

Ordering Information | *Note: Contact Customer Care at 1-800-743-2675 for other options.*



**1** Defines fiber count.  
002 = 2 fibers

**2** Select fiber code.  
K = 62.5 μm multimode (OM1)  
T = 50 μm multimode (OM2/OM3/OM4/OM4+)  
E = Single-mode (OS2) SMF-28e<sup>®</sup> fiber  
Z = Single-mode (OS2) SMF-28<sup>®</sup> Ultra fiber

**3** Defines cable type.  
5 = Zipcord

**4** Defines outer jacket.  
1 = Riser

**5** Defines fiber placement and markings  
31 = Zipcord cable, 2-fiber, ft markings

**6** Select cable outside diameter.  
1 = 2.8 mm  
3 = 2.0 mm  
4 = 1.6 mm

**7** Select performance option code.  
30 = 62.5 μm multimode (OM1)  
31 = 50 μm multimode (OM2)  
80 = 50 μm multimode (OM3)  
90 = 50 μm multimode (OM4)  
91 = 50 μm multimode (OM4+)  
31 = Single-mode (OS2)  
(Max. attenuation .65 / .65 / 0.5 dB/km)

**8** Defines cable type.  
- = Zipcord

**9** Defines special manufacturing code.  
24 = Standard for zipcord riser cables, 2 fibers

*Note: This cable is available in 12 different jacket colors – blue, orange, green, brown, slate, white, red, black, yellow, violet, rose and aqua. The colored jacket allows for easy visual identification of the cables while still providing all of the required environmental protection of an indoor/outdoor cable jacket. Black is the standard jacket color using the part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.*



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2019 Corning Optical Communications. All rights reserved.

CORNING