


Centrix™ Pigtailed Cassette

36 fiber, staggered LC APC duplex panels, single-fiber, single-mode (OS2)

CORNING

The Centrix™ platform is a high-density fiber management system that provides a balance of industry-leading density with innovative jumper routing. The system can be deployed in multiple applications including: central office, headend, FTTx, FTTCs and data center. Centrix platform supports up to 4,320 LC or 2,880 SC connector ports per standard 7-ft frame.

The Centrix™ system staggered cassette is designed to ensure maximum finger access and reduce the potential for inadvertent disconnects. Additionally, these cassettes include port mapping labels providing simple identification.



Part Number: CTXCPP3S-B3-2RH000

Specifications

General Specifications	
Application	Central Office, Headend
Product Type	Rack-Mountable Hardware
Cable Type	900 μm
Fiber Category	Single-mode (OS2)
Technology	Fusion Splice

Design - Hardware	
Fiber Count	36
Panel or Module Type	Centrix Cassette
Splice Protectors Type	Heat-shrink splice protection
Number of Splice Protectors	36
Connector Configuration	LC duplex
Connector Polish	APC

Mechanical Characteristics	
Dimensions (L x W x D)	13 mm x 318 mm x 298 mm

Centrix™ Pigtailed Cassette

36 fiber, staggered LC APC duplex panels, single-fiber, single-mode (OS2)



Optical Specification - Hardware

Module Insertion Loss, Typical (by 1300 nm)	0.25 dB
---	---------

Design Adapter

Adapter Type	LC
--------------	----

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Ordering Information

Part Number	CTXCPP3S-B3-2RH000
Product Description	Centrix™ pigtailed cassette, 36 fiber, staggered LC APC duplex panels, single-fiber, single-mode (OS2)

Shipping Information

Units per Delivery	1/1
Weight	1.0 kg



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2018 Corning Optical Communications. All rights reserved.

