Glass designation: UV CLEAR Code 8010

Color: White

Filter category : Chemtemperable, 100 % UV absorbing crown glass

Application : Ophtalmic lenses : Single vision, G&P progressive addition.

PHYSICAL PROPERTIES

Density : Linear Exp. Coef. :		2.48 68	g/cm3 10 ⁻⁷ / °C
,	Ann Di	502	°C

Ann. Pt 502 °C Strain Pt 469 °C

REFRACTIVE INDEX

Line		λ (nm)	Value			
F'	Cadmium	480.0	1.52966			
F	Hydrogen	486.1	1.52916			
е	Mercury	546.1	1.52519			
d	Helium	587.6	1.52310			
C'	Cadmium	643.8	1.52085			
С	Hydrogen	656.3	1.52040			
Abbe Number		ve	59.6			
		νd	59 7			

380 - 780 nm

Luminous transmission factor	91%
Transmission category	
ISO 8980-3	0

ULTRAVIOLET

VISIBLE

t(avg) 280 - 315 nm	< 0.1 %
Solar UV-B transmission factor	< 0.1 %

t(moy) 315 - 380 nm < 0.1 % Solar UV-A transmission factor < 0.1 %

BLUE LIGHT 380 - 500 nm

Blue light transmission factor 88%

TRAFFIC SIGNAL RECOGNITION


COATING & TEMPERING

(See also notes below)

Vacuum coating YES
Chemical tempering YES
Air tempering NO

CHEMICAL DURABILITY (class)

To water NF ISO 719 HGB3
To acid DIN 12-116 4
To alkalis ISO 695 A3



CORNING SAS - Ophthalmic PO Box Nr 90094 - Bagneaux sur Loing - F 77992 Nemours cédex - FRANCE

Glass designation: UV CLEAR Code 8010

Color: White

Glass type : Chemtemperable, 100 % UV absorbing crown glass

Application : Ophtalmic lenses : Single vision, G&P progressive addition.

Chemtempering: Recommended bath and cycle (no preheating nor postcooling):

Bath: Potassium Nitrate 99.5 % (Sodium nitrate 0,5% max) Time: 16 Hr

Silicic Acid 0.5 % θ °C : $450 \ ^{\circ}$ C

Air tempering:

This glass shall not be air tempered

Compatible Bariums:

This glass can not be used to manufacture fused multifocal lenses. There is no compatible bariums to be fused with this glass.

Coating:

Special attention is required to achieve an appropriate surface quality, including the selection of the cleaning products used after surfacing and before coating. The use of strong acidic solutions shall be avoided.

Properties according to ISO 14889

ISO 14889 Chapter 4.3.1

Physiological compatibility

The above glass products are not known to be physiologically incompatible, nor known to create a significant number of allergic reactions, when the lenses made out of these materials are used as intended by the manufacturer

ISO 14889 Chapter 4.3.2

Flammability

The above glass products are not flammable, and when tested as described in chapter 5.1 of ISO 14889, there is no continued combustion after withdrawal of the test rod.