





SOLO[®] All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

features and benefits |

Available with a proprietary track-resistant polyethylene (TRPE) jacket	Suitable for installations in electric field potentials up to 25 kV
Concentric, self-supporting cable design	Allows easy, one-step installation, using standard hardware and installation methods
Innovative waterblocking design	Eliminates the need for traditional flooding compound, providing efficient and craft-friendly cable preparation
SZ-stranded, loose tube design	Isolates fibers from installation and environmental rigors and facilitates midspan access

Corning Cable Systems SOLO[®] Cables are all-dielectric, self-supporting (ADSS) cables designed for easy and economical one-step installation in campus backbones with self-supporting installations where metallic messengers cannot be used. The loose tube design provides stable performance over a wide temperature range and is compatible with any telecommunications-grade optical fiber. This cable incorporates innovative waterblocking materials, eliminating the need for traditional flooding compound and providing efficient and craft-friendly cable preparation. While the concentric, self-supporting cable design allows easy, one-step installation, using standard hardware and installation methods, the SZ-stranded, loose tube design isolates optical fibers from installation and environmental rigors and facilitates midspan access. The ADSS cables are also available with a proprietary track-resistant polyethylene (TRPE) jacket suitable for installation in electric field potentials up to 25 kV.



SOLO® All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

specifications |

Temperatures

Storage: -40° to +70°C (-40° to +158°F)
 Installation: -30° to +70°C (-22° to +158°F)
 Operation: -40° to +70°C (-40° to +158°F)

Weight Count	Nominal Cable Diameter kg/km (lb/1000 ft)	Nominal Outer Diameter mm (in)	Minimum Bend Radius		Span Code
			Loaded cm (in)	Installed cm (in)	
2-72	138 (93)	13.5 (0.53)	20.3 (8.0)	13.5 (5.3)	2
	148 (99)	14.0 (0.55)	21.0 (8.3)	14.0 (5.5)	5
	193 (130)	16.2 (0.64)	24.3 (9.6)	16.2 (6.4)	A
	207 (139)	16.8 (0.66)	25.2 (9.9)	16.8 (6.6)	C
	212 (143)	17.1 (0.67)	25.7 (10.1)	17.1 (6.7)	E
73-96	181 (122)	15.5 (0.61)	23.3 (9.2)	15.5 (6.1)	4
	235 (158)	17.8 (0.70)	26.7 (10.5)	17.8 (7.0)	B
	239 (160)	18.0 (0.71)	27.0 (10.6)	18.0 (7.1)	C
	248 (167)	18.4 (0.72)	27.6 (10.9)	18.4 (7.2)	F
97-144	320 (215)	20.5 (0.81)	30.8 (12.1)	20.5 (8.1)	4
	329 (221)	20.8 (0.82)	31.2 (12.3)	20.8 (8.2)	A
	337 (226)	21.1 (0.83)	31.7 (12.5)	21.1 (8.3)	C
	354 (238)	21.8 (0.86)	32.7 (12.9)	21.8 (8.6)	F
145-216	281 (189)	19.7 (0.78)	29.6 (11.6)	19.7 (7.8)	2
	284 (191)	19.9 (0.78)	29.9 (11.8)	19.9 (7.8)	4
	332 (224)	21.5 (0.85)	32.3 (12.7)	21.5 (8.5)	8
	341 (229)	21.8 (0.86)	32.7 (12.9)	21.8 (8.6)	A
	349 (235)	22.1 (0.87)	33.2 (13.1)	22.1 (8.7)	B
240-288	421 (283)	23.9 (0.94)	35.8 (14.1)	23.9 (9.4)	2
	434 (292)	24.3 (0.96)	36.5 (14.4)	24.3 (9.6)	6
	449 (302)	24.8 (0.98)	37.2 (14.7)	24.8 (9.8)	A
	456 (306)	25.0 (0.98)	37.5 (14.8)	25.0 (9.8)	C
	464 (312)	25.3 (1.00)	38.0 (15.0)	25.3 (10.0)	E

Note: Dimensions, weights and span distances shown are for cables with polyethylene jackets. Diameters and weights are representative figures and may vary ± 5%. Contact Customer Service for additional options.

SOLO[®] All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

specifications | (continued)

Sag and Tension Information									
Fiber Count	Installation		NESC Light		NESC Medium		NESC Heavy		
	Span m (ft)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	
Span Code 2									
2-72	30 (100)	1.0	511 (115)	1.1	1098 (247)	2.2	1404 (316)	2.8	2151 (484)
	61 (200)	1.0	1022 (230)	1.3	1960 (441)	2.5	2458 (553)	3.3	3649 (821)
	91 (300)	1.0	1538 (346)	1.4	2742 (617)	2.7	3391 (763)	3.7	4951 (1114)
	122 (400)	1.0	2049 (461)	1.4	3478 (783)	2.9	4253 (957)	3.9	6152 (1384)
	152 (500)	1.0	2560 (576)	1.5	4178 (940)	3.1	5076 (1142)	-	- -
	183 (600)	1.0	3071 (691)	1.6	4853 (1092)	3.2	5862 (1319)	-	- -
	213 (700)	1.0	3582 (806)	1.6	5516 (1241)	3.3	6622 (1490)	-	- -
	244 (800)	1.0	4093 (921)	1.6	6160 (1386)	-	- -	-	- -
	274 (900)	1.0	4611 (1037)	1.7	6796 (1529)	-	- -	-	- -
Span Code 5									
2-72	122 (400)	1.0	2182 (491)	1.4	3787 (852)	2.7	4676 (1052)	3.6	6889 (1550)
	152 (500)	1.0	2729 (614)	1.4	4569 (1028)	2.3	5605 (1261)	3.8	8164 (1837)
	183 (600)	1.0	327 (6737)	1.5	5324 (1198)	2.9	6492 (1461)	3.9	9382 (2111)
	213 (700)	1.0	3818 (859)	1.5	6062 (1364)	3.0	7342 (1652)	4.1	10551 (2374)
	244 (800)	1.0	4364 (982)	1.5	6782 (1526)	3.1	8173 (1839)	-	- -
	274 (900)	1.0	4911 (1105)	1.5	7484 (1684)	3.2	8987 (2022)	-	- -
	305 (1000)	1.0	5458 (1228)	1.6	8178 (1840)	3.2	9782 (2201)	-	- -
	335 (1100)	1.0	6000 (1350)	1.6	8862 (1994)	3.3	10564 (2377)	-	- -
	366 (1200)	1.0	6547 (1473)	1.6	9538 (2146)	-	- -	-	- -
	396 (1300)	1.0	7093 (1596)	1.6	10204 (2296)	-	- -	-	- -
	Span Code A								
2-72	213 (700)	1.0	5049 (1136)	1.3	7560 (1701)	2.7	8964 (2017)	3.6	12876 (2897)
	244 (800)	1.0	5769 (1298)	1.4	8489 (1910)	2.8	10022 (2255)	3.7	14289 (3215)
	274 (900)	1.0	6489 (1460)	1.4	9400 (2115)	2.8	11053 (2487)	3.8	15667 (3525)
	305 (1000)	1.0	7213 (1623)	1.4	10302 (2318)	2.9	12062 (2714)	3.9	17009 (3827)
	335 (1100)	1.0	7933 (1785)	1.4	11187 (2517)	2.9	13058 (2938)	-	- -
	366 (1200)	1.0	8653 (1947)	1.4	12062 (2714)	3.0	14036 (3158)	-	- -
	396 (1300)	1.0	9373 (2109)	1.5	12929 (2909)	3.0	15004 (3376)	-	- -
	427 (1400)	1.0	10098 (2272)	1.5	13791 (3103)	3.0	15956 (3590)	-	- -
	457 (1500)	1.0	10818 (2434)	1.5	14640 (3294)	3.1	16902 (3803)	-	- -
	488 (1600)	1.0	11538 (2596)	1.5	15489 (3485)	-	- -	-	- -
	518 (1700)	1.0	12262 (2759)	1.5	16324 (3673)	-	- -	-	- -
	549 (1800)	1.0	12982 (2921)	1.5	17160 (3861)	-	- -	-	- -

Continued

SOLO[®] All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

specifications | (continued)

Sag and Tension Information									
Fiber Count	Installation		NESC Light		NESC Medium		NESC Heavy		
	Span m (ft)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	
Span Code C									
2-72	274 (900)	1.0	6960 (1566)	1.3	9996 (2249)	2.7	11720 (2637)	3.6	16653 (3747)
	305 (1000)	1.0	7733 (1740)	1.4	10960 (2466)	2.8	12800 (2880)	3.7	18089 (4070)
	335 (1100)	1.0	8507 (1914)	1.4	11911 (2680)	2.8	13867 (3120)	3.8	19493 (4386)
	366 (1200)	1.0	9280 (2088)	1.4	12853 (2892)	2.9	14916 (3356)	3.9	20871 (4696)
	396 (1300)	1.0	10053 (2262)	1.4	13787 (3102)	2.9	15951 (3589)	–	–
	427 (1400)	1.0	10831 (2437)	1.4	14707 (3309)	2.9	16973 (3819)	–	–
	457 (1500)	1.0	11604 (2611)	1.4	15622 (3515)	3.0	17982 (4046)	–	–
	488 (1600)	1.0	12378 (2785)	1.4	16529 (3719)	3.0	18982 (4271)	–	–
	518 (1700)	1.0	13151 (2959)	1.5	17431 (3922)	3.0	19978 (4495)	–	–
	549 (1800)	1.0	13924 (3133)	1.5	18324 (4123)	3.1	20960 (4716)	–	–
	579 (1900)	1.0	14698 (3307)	1.5	19218 (4324)	–	–	–	–
	610 (2000)	1.0	15471 (3481)	1.5	20102 (4523)	–	–	–	–
	640 (2100)	1.0	16244 (3655)	1.5	21245 (4721)	–	–	–	–
Span Code E									
2-72	335 (1100)	1.0	8671 (1951)	1.4	12311 (2770)	2.7	14351 (3229)	3.7	20324 (4573)
	366 (1200)	1.0	9462 (2129)	1.4	13284 (2989)	2.8	15440 (3474)	3.7	21764 (4897)
	396 (1300)	1.0	10249 (2306)	1.4	14249 (3206)	2.8	16516 (3716)	3.8	23178 (5215)
	427 (1400)	1.0	11040 (2484)	1.4	15204 (3421)	2.8	17578 (3955)	3.9	24569 (5528)
	457 (1500)	1.0	11827 (2661)	1.4	16151 (3634)	2.8	18627 (4191)	–	–
	488 (1600)	1.0	12613 (2838)	1.4	17093 (3846)	2.9	19667 (4425)	–	–
	518 (1700)	1.0	13404 (3016)	1.4	18022 (4055)	2.9	20698 (4657)	–	–
	549 (1800)	1.0	14191 (3193)	1.4	18951 (4264)	3.0	21716 (4886)	–	–
	579 (1900)	1.0	14982 (3371)	1.4	19871 (4471)	3.0	22724 (5113)	–	–
	610 (2000)	1.0	15769 (3548)	1.5	20787 (4677)	3.0	23729 (5339)	–	–
	640 (2100)	1.0	16556 (3725)	1.5	21698 (4882)	–	–	–	–
	671 (2200)	1.0	17347 (3903)	1.5	22600 (5085)	–	–	–	–
	701 (2300)	1.0	18133 (4080)	1.5	23502 (5288)	–	–	–	–
	731 (2400)	1.0	18880 (4248)	1.5	24400 (5490)	–	–	–	–

SOLO[®] All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

specifications | (continued)

Sag and Tension Information									
Fiber Count	Installation		NESC Light		NESC Medium		NESC Heavy		
	Span m (ft)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	
Span Code 4									
73-96	122 (400)	1.0	2689 (605)	1.3	4222 (950)	2.7	5058 (1138)	3.5	7289 (1640)
	152 (500)	1.0	3364 (757)	1.4	5111 (1150)	2.8	6076 (1367)	3.7	8662 (1949)
	183 (600)	1.0	4036 (908)	1.4	5973 (1344)	2.9	7053 (1587)	3.9	9964 (2242)
	213 (700)	1.0	4707 (1059)	1.4	6813 (1533)	3.0	8000 (1800)	4.0	11222 (2525)
	244 (800)	1.0	5382 (1211)	1.5	7636 (1718)	3.0	8929 (2009)	–	–
	274 (900)	1.0	6053 (1362)	1.5	8449 (1901)	3.1	9831 (2212)	–	–
	305 (1000)	1.0	6724 (1513)	1.5	9244 (2080)	3.2	10724 (2413)	–	–
	335 (1100)	1.0	7400 (1665)	1.5	10036 (2258)	3.2	11600 (2610)	–	–
	366 (1200)	1.0	8071 (1816)	1.6	10818 (2434)	–	–	–	–
	396 (1300)	1.0	8742 (1967)	1.6	11591 (2608)	–	–	–	–
Span Code B									
73-96	213 (700)	1.0	6120 (1377)	1.3	8444 (1900)	2.7	9764 (2197)	3.6	13698 (3082)
	244 (800)	1.0	6996 (1574)	1.3	9498 (2137)	2.7	10933 (2460)	3.7	15213 (3423)
	274 (900)	1.0	7871 (1771)	1.4	10538 (2371)	2.8	12076 (2717)	3.8	16711 (3760)
	305 (1000)	1.0	8742 (1967)	1.4	11564 (2602)	2.8	13204 (2971)	3.8	18160 (4086)
	335 (1100)	1.0	9618 (2164)	1.4	12578 (2830)	2.9	14316 (3221)	3.9	19578 (4405)
	366 (1200)	1.0	10493 (2361)	1.4	13582 (3056)	2.9	15409 (3467)	–	–
	396 (1300)	1.0	11369 (2558)	1.4	14578 (3280)	2.9	16493 (3711)	–	–
	427 (1400)	1.0	12240 (2754)	1.4	15569 (3503)	3.0	17564 (3952)	–	–
	457 (1500)	1.0	13116 (2951)	1.4	16551 (3724)	3.0	18627 (4191)	–	–
	488 (1600)	1.0	13991 (3148)	1.4	17524 (3943)	3.0	19680 (4428)	–	–
	518 (1700)	1.0	14867 (3345)	1.5	18498 (4162)	–	–	–	–
	549 (1800)	1.0	15738 (3541)	1.5	19462 (4379)	–	–	–	–
	Span Code C								
73-96	305 (1000)	1.0	8893 (2001)	1.3	11916 (2681)	2.7	13662 (3074)	3.7	18969 (4268)
	335 (1100)	1.0	9782 (2201)	1.4	12960 (2916)	2.8	14818 (3334)	3.8	20458 (4603)
	366 (1200)	1.0	10671 (2401)	1.4	14000 (3150)	2.8	15951 (3589)	3.8	21916 (4931)
	396 (1300)	1.0	11560 (2601)	1.4	15027 (3381)	2.8	17076 (3842)	3.9	23351 (5254)
	427 (1400)	1.0	12449 (2801)	1.4	16049 (3611)	2.9	18187 (4092)	–	–
	457 (1500)	1.0	13338 (3001)	1.4	17058 (3838)	2.9	19289 (4340)	–	–
	488 (1600)	1.0	14231 (3202)	1.4	18067 (4065)	2.9	20378 (4585)	–	–
	518 (1700)	1.0	15120 (3402)	1.4	19067 (4290)	3.0	21458 (4828)	–	–
	549 (1800)	1.0	16009 (3602)	1.4	20062 (4514)	3.0	22533 (5070)	–	–
	579 (1900)	1.0	16898 (3802)	1.4	21049 (4736)	3.0	23600 (5310)	–	–
	610 (2000)	1.0	17787 (4002)	1.5	22036 (4958)	–	–	–	–
	640 (2100)	1.0	18676 (4202)	1.5	23018 (5179)	–	–	–	–
	671 (2200)	1.0	19564 (4402)	1.5	23996 (5399)	–	–	–	–

Continued

SOLO[®] All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

Sag and Tension Information									
Fiber Count	Installation		NESC Light		NESC Medium		NESC Heavy		
	Span m (ft)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	
Span Code F									
73-96	366 (1200)	1.0	11076 (2492)	1.3	14582 (3281)	2.7	16627 (3741)	3.7	22964 (5167)
	396 (1300)	1.0	12000 (2700)	1.4	15653 (3522)	2.8	17804 (4006)	3.8	24476 (5507)
	427 (1400)	1.0	12920 (2907)	1.4	16720 (3762)	2.8	18969 (4268)	3.8	25960 (5841)
	457 (1500)	1.0	13844 (3115)	1.4	17782 (4001)	2.8	20120 (4527)	3.9	27422 (6170)
	488 (1600)	1.0	14769 (3323)	1.4	14237 (1883)	2.9	21258 (4783)	–	–
	518 (1700)	1.0	15689 (3530)	1.4	19876 (4472)	2.9	22391 (5038)	–	–
	549 (1800)	1.0	16613 (3738)	1.4	20916 (4706)	2.9	23516 (5291)	–	–
	579 (1900)	1.0	17538 (3946)	1.4	21951 (4939)	2.9	24631 (5542)	–	–
	610 (2000)	1.0	18458 (4153)	1.4	22978 (5170)	3.0	25738 (5791)	–	–
	640 (2100)	1.0	19382 (4361)	1.4	24004 (5401)	3.0	26840 (6039)	–	–
	671 (2200)	1.0	20307 (4569)	1.4	25022 (5630)	3.0	27933 (6285)	–	–
	701 (2300)	1.0	21227 (4776)	1.4	26040 (5859)	–	–	–	–
	731 (2400)	1.0	22151 (4984)	1.4	27053 (6087)	–	–	–	–
	762 (2500)	1.0	23076 (5192)	1.5	28062 (6314)	–	–	–	–

SOLO[®] All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

PRETERMINATED SYSTEMS | CABLES | CONNECTORS | CABLE ASSEMBLIES | HARDWARE | COPPER CONNECTIVITY | SPlice AND TEST EQUIPMENT | TRAINING |

Sag and Tension Information									
Fiber Count	Installation		NESC Light		NESC Medium		NESC Heavy		
	Span m (ft)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	
Span Code 4									
97-144	183 (600)	1.0	7084 (1594)	1.3	8844 (1990)	2.6	9778 (2200)	3.6	12876 (2897)
	213 (700)	1.0	8267 (1860)	1.3	10147 (2283)	2.6	11164 (2512)	3.7	14564 (3277)
	244 (800)	1.0	9444 (2125)	1.3	11431 (2572)	2.7	12524 (2818)	3.8	16204 (3646)
	274 (900)	1.0	10627 (2391)	1.3	12707 (2859)	2.7	13867 (3120)	3.9	17813 (4008)
	305 (1000)	1.0	11809 (2657)	1.3	13973 (3144)	2.7	15196 (3419)	–	–
	335 (1100)	1.0	12987 (2922)	1.3	15231 (3427)	2.8	16511 (3715)	–	–
	366 (1200)	1.0	14169 (3188)	1.3	16480 (3708)	–	–	–	–
Span Code A									
97-144	213 (700)	1.0	8502 (1913)	1.3	10498 (2362)	2.5	11631 (2617)	3.5	15404 (3466)
	244 (800)	1.0	9716 (2186)	1.3	11836 (2663)	2.6	13053 (2937)	3.6	17147 (3858)
	274 (900)	1.0	10929 (2459)	1.3	13160 (2961)	2.6	14458 (3253)	3.7	18853 (4242)
	305 (1000)	1.0	12142 (2732)	1.3	14476 (3257)	2.7	15849 (3566)	3.8	20524 (4618)
	335 (1100)	1.0	13360 (3006)	1.3	15782 (3551)	2.7	17222 (3875)	–	–
	366 (1200)	1.0	14573 (3279)	1.3	17080 (3843)	2.7	18582 (4181)	–	–
	396 (1300)	1.0	15787 (3552)	1.3	18373 (4134)	2.7	19938 (4486)	–	–
	427 (1400)	1.0	17000 (3825)	1.3	19658 (4423)	2.8	21280 (4788)	–	–
	457 (1500)	1.0	18218 (4099)	1.3	20938 (4711)	–	–	–	–
Span Code C									
97-144	274 (900)	1.0	11231 (2527)	1.3	13587 (3057)	2.6	15004 (3376)	3.5	19791 (4453)
	305 (1000)	1.0	12480 (2808)	1.3	14960 (3366)	2.6	16449 (3701)	3.6	21551 (4849)
	335 (1100)	1.0	13729 (3089)	1.3	16302 (3668)	2.6	17880 (4023)	3.7	23280 (5238)
	366 (1200)	1.0	14978 (3370)	1.3	17644 (3970)	2.7	19298 (4342)	3.7	24982 (5621)
	396 (1300)	1.0	16227 (3651)	1.3	18982 (4271)	2.7	20702 (4658)	–	–
	427 (1400)	1.0	17471 (3931)	1.3	20311 (4570)	2.7	22098 (4972)	–	–
	457 (1500)	1.0	18720 (4212)	1.3	21636 (4868)	2.7	23484 (5284)	–	–
	488 (1600)	1.0	19969 (4493)	1.3	22956 (5165)	2.7	24862 (5594)	–	–
	518 (1700)	1.0	21218 (4774)	1.3	24271 (5461)	–	–	–	–
	549 (1800)	1.0	22467 (5055)	1.3	25582 (5756)	–	–	–	–

Continued

SOLO[®] All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

Sag and Tension Information									
Fiber Count	Installation		NESC Light		NESC Medium		NESC Heavy		
	Span m (ft)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)
Span Code F									
97-144	366 (1200)	1.0	15782 (3551)	1.3	18707 (4209)	2.6	20564 (4627)	3.5	27040 (6084)
	396 (1300)	1.0	17098 (3847)	1.3	20138 (4531)	2.6	22071 (4966)	3.6	28867 (6495)
	427 (1400)	1.0	18413 (4143)	1.3	21547 (4848)	2.6	23564 (5302)	3.6	30667 (6900)
	457 (1500)	1.0	19729 (4439)	1.3	22956 (5165)	2.6	25049 (5636)	3.6	32444 (7300)
	488 (1600)	1.0	21044 (4735)	1.3	24360 (5481)	2.6	26520 (5967)	3.7	34204 (7696)
	518 (1700)	1.0	22360 (5031)	1.3	25760 (5796)	2.6	27987 (6297)	–	–
	549 (1800)	1.0	23676 (5327)	1.3	27151 (6109)	2.7	29444 (6625)	–	–
	579 (1900)	1.0	24991 (5623)	1.3	28542 (6422)	2.7	30898 (6952)	–	–
	610 (2000)	1.0	26307 (5919)	1.3	29929 (6734)	2.7	32342 (7277)	–	–
	640 (2100)	1.0	27622 (6215)	1.3	31311 (7045)	2.7	33782 (7601)	–	–
	671 (2200)	1.0	28938 (6511)	1.3	32689 (7355)	2.7	35213 (7923)	–	–
	701 (2300)	1.0	30253 (6807)	1.3	34067 (7665)	–	–	–	–

SOLO[®] All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

TRAINING | SPlice AND TEST EQUIPMENT | COPPER CONNECTIVITY | HARDWARE | CABLE ASSEMBLIES | CONNECTORS | CABLES | PRETERMINATED SYSTEMS

Sag and Tension Information									
Fiber Count	Installation		NESC Light		NESC Medium		NESC Heavy		
	Span m (ft)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	
Span Code 2									
145-216	61 (200)	1.0	2018 (454)	1.2	2942 (662)	2.3	3396 (764)	3.0	4840 (1089)
	91 (300)	1.0	3027 (681)	1.2	4204 (946)	2.5	4796 (1079)	3.3	6680 (1503)
	122 (400)	1.0	4036 (908)	1.3	5418 (1219)	2.6	6120 (1377)	3.5	8387 (1887)
	152 (500)	1.0	5044 (1135)	1.3	6596 (1484)	2.7	7396 (1664)	3.7	10009 (2252)
	183 (600)	1.0	6053 (1362)	1.3	7747 (1743)	2.7	8636 (1943)	–	–
	213 (700)	1.0	7062 (1589)	1.3	8880 (1998)	2.8	9849 (2216)	–	–
	244 (800)	1.0	8071 (1816)	1.4	9996 (2249)	–	–	–	–
Span Code 4									
145-216	122 (400)	1.0	4169 (938)	1.2	5667 (1275)	2.5	6440 (1449)	3.3	8978 (2020)
	152 (500)	1.0	5213 (1173)	1.3	6911 (1555)	2.6	7800 (1755)	3.4	10729 (2414)
	183 (600)	1.0	6253 (1407)	1.3	8124 (1828)	2.6	9116 (2051)	3.6	12404 (2791)
	213 (700)	1.0	7298 (1642)	1.3	9320 (2097)	2.7	10404 (2341)	3.7	14031 (3157)
	244 (800)	1.0	8342 (1877)	1.3	10498 (2362)	2.7	11667 (2625)	–	–
	274 (900)	1.0	17147 (3858)	1.3	11662 (2624)	2.8	12911 (2905)	–	–
	305 (1000)	1.0	18658 (4198)	1.4	12813 (2883)	–	–	–	–
	335 (1100)	1.0	20142 (4532)	1.4	13956 (3140)	–	–	–	–
Span Code 8									
145-216	152 (500)	1.0	6129 (1379)	1.2	7773 (1749)	2.5	8702 (1958)	3.3	11911 (2680)
	183 (600)	1.0	7356 (1655)	1.2	9173 (2064)	2.5	10204 (2296)	3.4	13809 (3107)
	213 (700)	1.0	8578 (1930)	1.3	10547 (2373)	2.6	11680 (2628)	3.5	15649 (3521)
	244 (800)	1.0	9804 (2206)	1.3	11907 (2679)	2.6	13129 (2954)	3.6	17436 (3923)
	274 (900)	1.0	11031 (2482)	1.3	13253 (2982)	2.6	14556 (3275)	–	–
	305 (1000)	1.0	12258 (2758)	1.3	14631 (3292)	2.7	15964 (3592)	–	–
	335 (1100)	1.0	13480 (3033)	1.3	15911 (3580)	2.7	17360 (3906)	–	–
	366 (1200)	1.0	14707 (3309)	1.3	17227 (3876)	–	–	–	–
Span Code A									
145-216	183 (600)	1.0	7556 (1700)	1.2	9453 (2127)	2.5	10560 (2376)	3.3	14422 (3245)
	213 (700)	1.0	8813 (1983)	1.2	10880 (2448)	2.5	12089 (2720)	3.4	16351 (3679)
	244 (800)	1.0	10076 (2267)	1.3	12293 (2766)	2.5	13596 (3059)	3.5	18227 (4101)
	274 (900)	1.0	11333 (2550)	1.3	13680 (3078)	2.6	15080 (3393)	3.5	20058 (4513)
	305 (1000)	1.0	12591 (2833)	1.3	15058 (3388)	2.6	16542 (3722)	–	–
	335 (1100)	1.0	13853 (3117)	1.3	16431 (3697)	2.7	17991 (4048)	–	–
	366 (1200)	1.0	15111 (3400)	1.3	17791 (4003)	2.7	19431 (4372)	–	–
	396 (1300)	1.0	16369 (3683)	1.3	19147 (4308)	2.7	20853 (4692)	–	–
	427 (1400)	1.0	17631 (3967)	1.3	20493 (4611)	–	–	–	–

Continued

SOLO[®] All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

Sag and Tension Information										
Fiber Count	Installation			NESC Light		NESC Medium		NESC Heavy		
	Span m (ft)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	
Span Code B										
145-216	244 (800)	1.0	10311 (2320)	1.2	12631 (2842)	2.5	14018 (3154)	3.3	18947 (4263)	
	274 (900)	1.0	11604 (2611)	1.3	14071 (3166)	2.5	11604 (2611)	3.4	20858 (4693)	
	305 (1000)	1.0	12893 (2901)	1.3	15489 (3485)	2.6	17067 (3840)	3.5	22733 (5115)	
	335 (1100)	1.0	14182 (3191)	1.3	16902 (3803)	2.6	18564 (4177)	3.6	24569 (5528)	
	366 (1200)	1.0	15471 (3481)	1.3	18307 (4119)	2.6	20049 (4511)	–	–	–
	396 (1300)	1.0	16760 (3771)	1.3	19702 (4433)	2.6	21520 (4842)	–	–	–
	427 (1400)	1.0	18049 (4061)	1.3	21089 (4745)	2.7	22982 (5171)	–	–	–
	457 (1500)	1.0	19373 (4359)	1.3	22471 (5056)	2.7	24431 (5497)	–	–	–
	488 (1600)	1.0	20671 (4651)	1.3	23844 (5365)	–	–	–	–	–

SOLO[®] All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

TRAINING | SPlice AND TEST EQUIPMENT | COPPER CONNECTIVITY | HARDWARE | CABLE ASSEMBLIES | CONNECTORS | CABLES | PRETERMINATED SYSTEMS

Sag and Tension Information									
Fiber Count	Installation		NESC Light		NESC Medium		NESC Heavy		
	Span m (ft)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	
Span Code 2									
217-288	91 (300)	1.0	4636 (1043)	1.1	5747 (1293)	2.3	6298 (1417)	3.0	8276 (1862)
	122 (400)	1.0	6178 (1390)	1.2	7449 (1676)	2.3	8093 (1821)	3.2	10440 (2349)
	152 (500)	1.0	7724 (1738)	1.2	9116 (2051)	2.4	9840 (2214)	3.4	12516 (2816)
	183 (600)	1.0	9267 (2085)	1.2	10760 (2421)	2.5	11551 (2599)	3.5	14520 (3267)
	213 (700)	1.0	10813 (2433)	1.2	12391 (2788)	2.5	13240 (2979)	–	– –
	244 (800)	1.0	12356 (2780)	1.2	14009 (3152)	2.5	14911 (3355)	–	– –
	274 (900)	1.0	13902 (3128)	1.3	15613 (3513)	–	– –	–	– –
Span Code 6									
217-288	183 (600)	1.0	9613 (2163)	1.2	11227 (2526)	2.4	12200 (2745)	3.2	15804 (3556)
	213 (700)	1.0	11213 (2523)	1.2	12942 (2912)	2.4	13996 (3149)	3.3	17942 (4037)
	244 (800)	1.0	12818 (2884)	1.2	14644 (3295)	2.4	15769 (3548)	3.4	20031 (4507)
	274 (900)	1.0	14418 (3244)	1.2	16333 (3675)	2.5	17524 (3943)	3.5	22080 (4968)
	305 (1000)	1.0	16022 (3605)	1.2	18013 (4053)	2.5	19262 (4334)	3.5	24098 (5422)
	335 (1100)	1.0	17622 (3965)	1.2	19684 (4429)	2.5	20991 (4723)	–	– –
	366 (1200)	1.0	19227 (4326)	1.3	21347 (4803)	2.6	22707 (5109)	–	– –
	396 (1300)	1.0	20827 (4686)	1.3	23009 (5177)	–	– –	–	– –
Span Code A									
217-288	305 (1000)	1.0	16596 (3734)	1.2	18729 (4214)	2.4	20169 (4538)	3.4	25702 (5783)
	335 (1100)	1.0	18258 (4108)	1.2	20471 (4606)	2.5	21982 (4946)	3.4	27827 (6261)
	366 (1200)	1.0	19916 (4481)	1.2	22209 (4997)	2.5	23782 (5351)	3.5	29920 (6732)
	396 (1300)	1.0	21578 (4855)	1.2	23942 (5387)	2.5	25573 (5754)	3.5	31987 (7197)
	427 (1400)	1.0	23236 (5228)	1.2	25667 (5775)	2.5	27356 (6155)	–	– –
	457 (1500)	1.0	24898 (5602)	1.3	27387 (6162)	2.5	29129 (6554)	–	– –
	488 (1600)	1.0	26556 (5975)	1.3	29102 (6548)	2.5	30893 (6951)	–	– –
	518 (1700)	1.0	28213 (6348)	1.3	30818 (6934)	–	– –	–	– –
	549 (1800)	1.0	29876 (6722)	1.3	32524 (7318)	–	– –	–	– –
Span Code C									
217-288	335 (1100)	1.0	18564 (4177)	1.2	20827 (4686)	2.4	22422 (5045)	3.4	28587 (6432)
	366 (1200)	1.0	20253 (4557)	1.2	22596 (5084)	2.4	24262 (5459)	3.4	30742 (6917)
	396 (1300)	1.0	21942 (4937)	1.2	24360 (5481)	2.5	26093 (5871)	3.4	32867 (7395)
	427 (1400)	1.0	23636 (5318)	1.2	26120 (5877)	2.5	27911 (6280)	3.5	34973 (7869)
	457 (1500)	1.0	25316 (5696)	1.2	27871 (6271)	2.5	29724 (6688)	–	– –
	488 (1600)	1.0	27004 (6076)	1.2	29622 (6665)	2.5	31524 (7093)	–	– –
	518 (1700)	1.0	28693 (6456)	1.3	31369 (7058)	2.5	33324 (7498)	–	– –
	549 (1800)	1.0	30378 (6835)	1.3	33107 (7449)	2.5	35111 (7900)	–	– –
	579 (1900)	1.0	32067 (7215)	1.3	34844 (7840)	–	– –	–	– –
	610 (2000)	1.0	33756 (7595)	1.3	36582 (8231)	–	– –	–	– –

Continued

SOLO® All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

Sag and Tension Information									
Fiber Count	Installation			NESC Light		NESC Medium		NESC Heavy	
	Span m (ft)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)	Sag %	Tension N (lbf)
Span Code E									
217-288	396 (1300)	1.0	22324 (5023)	1.2	24813 (5583)	2.4	26622 (5990)	3.4	33733 (7590)
	427 (1400)	1.0	24040 (5409)	1.2	26604 (5986)	2.5	28480 (6408)	3.4	35893 (8076)
	457 (1500)	1.0	25760 (5796)	1.2	28391 (6388)	2.5	30329 (6824)	3.5	38036 (8558)
	488 (1600)	1.0	27476 (6182)	1.2	30178 (6790)	2.5	32173 (7239)	3.5	40156 (9035)
	518 (1700)	1.0	29196 (6569)	1.2	31956 (7190)	2.5	34004 (7651)	–	–
	549 (1800)	1.0	30911 (6955)	1.2	33729 (7589)	2.5	35836 (8063)	–	–
	579 (1900)	1.0	32627 (7341)	1.3	35502 (7988)	2.5	37658 (8473)	–	–
	610 (2000)	1.0	34347 (7728)	1.3	37271 (8386)	2.5	39471 (8881)	–	–
	640 (2100)	1.0	36062 (8114)	1.3	39036 (8783)	–	–	–	–
	671 (2200)	1.0	37778 (8500)	1.3	40800 (9180)	–	–	–	–

SOLO® All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

transmission performance |

Fiber Code	K	T	E	E
Performance Option Code	30	31	01	00
Optical Fiber Type (µm)	62.5/125 µm	50/125 µm	Single-mode*	Single-mode*
ISO/IEC 11801 Nomenclature	OM1	OM2	OS2	OS2
Wavelength (nm)	850/1300	850/1300	1310/1383/1550	1310/1383/1550
Maximum Attenuation (dB/km)	3.4/1.0	3.0/1.0	0.4/0.4/0.3	0.35/0.35/0.25
Minimum Over Filled Launch (OFL) Bandwidth (MHz•km)	200/500	700/500	- / - / -	- / - / -
Minimum Effective Modal Bandwidth (MHz•km)	220/ -	950/ -	- / - / -	- / - / -
Serial 1 Gigabit Ethernet Distance (m)	300/550	750/600	5000/ - / -	5000/ - / -
Serial 10 Gigabit Ethernet Distance (m)	33/ -	150/ -	10000/ - /40000	10000/ - /40000

* ITU 652.D compliant.

SOLO® All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable Systems Product

ordering information | Contact Customer Service at 800-743-2671 for other options.

<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	A	<input type="checkbox"/>	-	T	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	A	2	0
1	2	3	4	5	6		7	8	9	10	11	12	13	14

|1-3

Select fiber count (002 to 288).

|4

Select fiber code (see Transmission Performance table).

|5 / 12

Defines cable type.
A / A = SOLO® Dual-Jacket Cable

|6

Select jacket.
E = PE jacket (standard)
A = TRPE jacket

|7

Defines fiber placement.
T = 12 fiber/buffer tube (standard)

|8

Select length markings.
3 = Markings in meters
4 = Markings in feet (standard)

|9

Select tensile strength. (see Span Codes in Sag and Tension Tables).

|10-11

Select performance option code (see Transmission Performance table).

|13-14

Defines special requirements.
20 = No special requirements

Notes:

1) Please contact Corning Cable Systems Engineering Services at 800-743-2671 for installation, advice or information regarding mounting hardware.

SOLO[®] All-Dielectric Self-Supporting Cables, 2-288 Fibers

notes |

A Corning Cable Systems Product

TRAINING | SPLICE AND TEST EQUIPMENT | COPPER CONNECTIVITY | HARDWARE | CABLE ASSEMBLIES | CONNECTORS | CABLES | PRETERMINATED SYSTEMS

SOLO[®] All-Dielectric Self-Supporting Cables, 2-288 Fibers

A Corning Cable
Systems Product

Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

Corning Cable Systems reserves the right to improve, enhance and modify the features and specifications of Corning Cable Systems products without prior notification. SOLO is a registered trademark of Corning Cable Systems Brands, Inc. All other trademarks are the properties of their respective owners. Corning Cable Systems is ISO 9001 certified. © 2012, 2017 Corning Cable Systems. All rights reserved. Published in the USA. EVO-403-EN / November 2017