



Corning 7056 Alkali Borosilicate Glass

Color	White
Glass Type	Hard Crown
Application	Optical, electronic, and Kovar sealing

Mechanical Properties

	Metric	English
Density	2.29 g/cm ³	143 lb/ft ³
Young's Modulus	6.4 x 10 ³ kg/mm ²	9.2 x 10 ⁶ psi
Poisson's Ratio	0.21	
Shear Modulus	2.7 x 10 ³ kg/mm ²	3.8 x 10 ⁶ psi

Viscosity

Working Point (10 ⁴ poise)	1058 °C	1936 °F
Softening Point (10 ^{7.6} poise)	718 °C	1324 °F
Annealing Point (10 ¹³ poise)	512 °C	954 °F
Strain Point (10 ¹⁴ poise)	472 °C	882 °F

Thermal

Linear Expansion Coefficient (0 - 300 °C)	51.5 x 10 ⁻⁷ / °C	28.5 x 10 ⁻⁷ / °F
Linear Expansion Coefficient (25 °C to set point 477 °C)	54.5 x 10 ⁻⁷ / °C	30.0 x 10 ⁻⁷ / °F

Optical

Refractive Index			
Line		λ (nm)	Value
F'	Cadmium	480.0	1.49300
F	Hydrogen	486.1	1.49200
e	Mercury	546.1	1.48900
d	Helium	587.6	1.48640
D	Sodium	589.3	1.48635
C'	Cadmium	643.8	1.48550
C	Hydrogen	656.3	1.48500
Abbe Number		ve	65.4
		vd	65.5

Electrical

Log ₁₀ Volume Resistivity at 250 °C	10.3 ohm-cm
Log ₁₀ Volume Resistivity at 350 °C	8.4 ohm-cm
Dielectric Constant at 20 °C, 1 MHz	5.7
Loss Tangent at 20 °C, 1 MHz	0.27%

Transmission

Visible	380 - 780 nm
Luminous Transmission Factor (10 mm thickness)	91%
Color- Minimum R Value (T400/T650) 5.5 mm thickness	0.90
Light Absorption or Beta Value	Maximum 1.5% / cm

$$\text{Beta Value} = \frac{((1 - r)^2 - T)}{((1 - r)^2 \cdot t)}$$
$$r: \frac{(nd - 1)}{(nd + 1)}^2$$

t: length of the sample in cm

T: Average transmission at 450, 507.7, 529.8, 543.7, 550, 555.4, 566.3, 576.9, 587.9, 600.1, 615.2, 639.7, 650 nm


Coating and Tempering

Vacuum Coating	YES
Chemical Tempering	N/A
Air Tempering	N/A

Chemical Durability (class)

To Water; NF ISO 719	N/A
To Acid; DIN 12-116	N/A
To Alkalis; ISO 695	N/A

7056 Glass Strips Specification
Annealing Point and Thermal Expansion Coefficient



CORNING

Corning SAS - Specialty Glass

Rue St Laurent - CS 10243 Bagneaux sur Loing
77797 Nemours Cedex - FRANCE

©2017 Corning Incorporated. All rights reserved.

Corning is a registered trademark of Corning Incorporated.

030617_rev b