

### **Carrier Innovation**



first low-loss optical fiber for communication networks

1978

Developed loose

tube fiber optic

cable design



Developed first CATV Node Assembly



connector -First-known, commercially available, field-mounted connector for FTTx indoor and outdoor use with no splice, gel, or adhesives



Clear Track fiber pathway answers demand for small-footprint, virtually invisible fiber deployment option

018



Acquired substantially all of 3M's highbandwidth products, expanding the optical solutions for our customers and improving access to broadband connectivity

1990

Fiber optic splice closure 2178 created for buried, belowgrade, aerial, and pole-mounted deployments

2005



SLiC® aerial closure released as free-breathing, weather-resistant, single-piece closure for aerial applications



7 million homes passed with OptiTip® connectors

First domestic ribbon cable invented

2007



ClearCurve® fiber revolutionized fiber installation in the most challenging environments



Launched with Binderless FastAccess® technology with industry-leading

MiniXtend® cable fiber density



Introduced Pushlok™ connector technology enabling the smallestform-factor preconn solutions available. Further offered Pushlok connector technology to the FlexNAP™ system with single-fiber connectors.

2004

Preterminated OptiTap® connector-enabled products became an industry standard and spurred OptiTip® connector and FlexNAP™ system development facilitating mass FTTH deployments



Centrix™ system was developed to support highdensity solutions for central office applications

industry's first solution to offer a combination single-fiber connection points, making it easier

Launched the FlexNAP multiuse system, the of multifiber and to quickly deploy FTTx networks







## Contents

Network Architectures	4
Deployment Methods	6
Central Office/Headend Solutions	10
Optical Splice Enclosures	12
Cable Assemblies	14
Optical Cables	16
Local Convergence Point	19
Closures and Terminals	22
FlexNAP™ System	25
Outside Plant Terminals	28
Multidwelling Unit (MDU) Terminals and NIDs	32
Orop Assemblies	35
Residential Hardware	39
Bulk Drop Cables	41
Field-Installable Connectors	44
Wireless Convergence	46

### Connect to the Corning Advantage

Each fiber-to-the-home (FTTH) deployment presents unique challenges – and we can help. With over 15 years' experience passing more than 70 million homes, we've set the standard for innovative, field-proven FTTH solutions.

Our portfolio of products and engineering support is designed to address your specific challenges from speed of deployment, labor and cost considerations, performance requirements, future readiness, and more.

To get started, use this quick selection guide to help determine the right architecture, deployment method, and products you need to do the job right the first time.

Evolve your network. Transform the world.





## Network Architectures

Connect to our experience passing over 70 million homes with the most prevalent architectures in all-fiber networks. Whether you're deploying active systems, PON technologies or converged networks, we can help you find success with fiber-rich designs or fiber-lean architectures — or a blended architecture, if that's what's best for your unique environment. As a leader in global FTTH deployments and innovation, whichever deployment scenario you choose from the following table, we have a solution that will deliver value that's right for you.

To learn more, visit us at www.corning.com/ftth-architectures

	Home Run	Centralized Split	Distributed Split	Distributed Tap
CORNING				
Consolidated Point for Cable and Splicing Management	Yes	Yes	No	No
Local Aggregation Point	Cabinet	Splitter cabinet	Splitter cabinet/closure/terminal	Splitter closure/terminal
Upfront Network CapEx	High	Moderate	Low	Low
Fiber-Lean Feeder/ Distribution System	Rich feeder and distribution cables	Leaner feeder than home run	Leaner feeder and distribution than home run; leaner distribution than centralized split	Ultra Lean feeder and distribution
OLT Ports Efficiency	Best	Best	Moderate to Low	Moderate
Supports Efficient Growth Strategy	High	High to moderate	Moderate to low	Low
Split Ratios Flexibility	High	High	Moderate	Moderate
Easily Adaptable	Best	Best	Moderate	Moderate to low
Quick Facts	Typically deployed to subscribers within five miles of central office in conjunction with centralized split and distributed split architectures  Home run architectures offer dedicated fiber from CO/HE to each subscriber with no splitters in the field, resulting in the most fiber-rich network architecture  Needed when planning active Ethernet systems	<ul> <li>Most common architecture deployed in the United States and Canada</li> <li>A single, centralized location for housing splitters in the field optimize OLT ports while leaning out the feeder network</li> </ul>	<ul> <li>Gaining popularity in the United States based on widespread success in Latin America and Europe</li> <li>By distributing or cascading splits in two or more field locations, the physical size of products in the field can shrink in size as the ports at each location are shared until the last access point</li> </ul>	<ul> <li>Asymmetric/Uneven split terminals allow for single-fiber distribution of concatenated terminals</li> <li>Ideally suited for environments where natural barriers restrict network growth</li> <li>Routes are custom configured to optimize link loss</li> <li>Most fiber lean architecture shown</li> </ul>




Your successful deployment is a delicate balance of budget, timing, labor, and other variables. An achievable project plan hinges on your ability to carefully choose the deployment method that maximizes your resources. Regardless of your network architecture type, you can deploy a future-ready FTTH network using an end-to-end preconnectorized method, a fully spliced method, or a mix of preconnectorized and spliced segments. Using what you know about the skill level of your labor and what's required of your network, take advantage of the following table to select your preferred deployment method.

	Full Preconnectorized	Preconnectorized	Full Splice	
CORNING				
Architecture	Home run, centralized, distributed	Home run, centralized, distributed	Home run, centralized, distributed	
Installation Type	Greenfield/brownfield	Greenfield/brownfield	Greenfield/brownfield	
Speed of Deployment (HP)	Fast	Moderate	Slow	
Subscriber Connection Speed (HC)	Fast	Fast	Slow	
Optimal Method of Build	Aerial, duct	Aerial, duct, direct buried	Aerial, duct, direct buried	
Optimal Subscriber Density	Medium to high	Low to high	Low to medium	
Design Verification/Planning	High	Moderate	Low	
Preconnectorized	Yes, for terminals, drops, and lateral cable runs	Yes, for subscriber drops	No	
Splices in the Field	Low	Moderate	High	
Labor Skill Level	Low	Moderate	High	
Installation Risk due to Labor Variability	Low	Moderate	Moderate to high	
Scalable for Mass Deployment	Best	Fair	Poor	
Deferability	High	Moderate	Low	
Quick Facts	<ul> <li>Preinstalled "plug-and-play" network access points mean simplicity, speed, and profitability for you and the fastest turn-up for your subscribers</li> <li>Splicing is concentrated at splitter cabinets</li> </ul>	<ul> <li>Enables fast installation of subscriber drops by utilizing hardened connectors at terminals</li> <li>Splicing extends to distribution access points as well as splitter cabinet</li> </ul>	<ul> <li>Allows for the least amount of pre-engineering up front</li> <li>Requires skilled labor splicing at all access points and subscriber premises</li> </ul>	



# Fiber in Single-Family Units (SFU)



- A Central Office/Headend (page 10)  $\circ$  and (page 14)  $\circ$  Network electronics combine and disperse signals to a specified serving area.
- B Optical Feeder Cable (page 16) **©**Fiber optic cables feed small distribution-serving areas.
- C Local Convergence Point (page 19) 
  In centralized and distributed split architectures, the field splitters are managed in this consolidated splice point.

- D Optical Distribution Cable (page 16) and (page 41) Bulk or preterminated cable solutions extend into neighborhoods and along city streets to cover the desired serving area.
- Discrete locations along the cable path allow for subscriber access to the distribution cable through closures or terminals.
- **Subscriber Drop** (page 35) **3** and (page 41) **3** The final piece connects the customer premise electronics to the assigned network access point.

< 🖍 >

# Fiber in Multidwelling Units (MDU)

### A Outside Demarcation Point (page 19) 6

Most MDU scenarios feature a demarcation point outside the building. Multiple small MDUs are often fed by distribution cabinets in the outside plant.

- Inside the Basement (page 20) of and (page 32) of Medium- to large-sized buildings often have a dedicated splitter cabinet supporting anywhere from 32 to 864 living units.
- C At the Floor (page 31) 
  Riser cables feed terminals on the floor and serve as the transition point from riser to horizontal cabling. Some buildings require a dedicated terminal on each floor, whereas other buildings use one terminal serving several adjacent floors.
- In medium- and large-sized MDUs, horizontal drop cables run down hallways providing an access point for subscribers to connect. In small MDUs, drop cables home run to the cabinet/splitter terminal.







# Central Office/Headend Solutions

The central office/headend (CO/HE) is the foundation needed to support demand for increased connectivity, capacity, and speed. To simplify the design and deployment of your CO/HE, we've developed versatile product families that deliver industry-leading density, enable improved scalability, and provide the lowest total cost of ownership. Whether utilizing splitter technology or xWDM optical devices paired with high-density connectors, we can help you plan and choose the right products to overlay these different PONs effectively. Use the following table to pinpoint the product set within our portfolio that will work best for your network.

To learn more, visit us at www.corning.com/central-office-design-guide

#### **High Density Medium Density** CORNING Centrix™ System Eclipse® Hardware Closet Connector Housing (CCH) EDGE™/EDGE8® Solutions Central office Headend Optical cross-connect cabinets Remote terminals Remote terminals, optical cross-connect cabinets Centrix GR-449 Certified frame. 19-in or 23-in 19-in or 23-in with rear cable access 19-in or 23-in 19-in or 23-in racks with front and rear access 2.880 SC/4.320 LC 1.440 SC 1,440 (864 with PON splitters) 5,760 LC (3,840 with PON splitters) 2,880 with 24-port cassettes LC No Loose Tube: outdoor dielectric, indoor/outdoor, Loose Tube: outdoor dielectric, outdoor Loose Tube: outdoor dielectric, indoor/ riser, plenum, and outdoor micro cables armored, indoor/outdoor, and riser cables outdoor, and riser cables Preterminated assemblies with plenum Ribbon: outdoor dielectric, indoor/outdoor, Ribbon: outdoor dielectric, outdoor armored, Ribbon: outdoor dielectric, indoor/ non-armored or plenum armored cables plenum and riser cables indoor/outdoor, riser and plenum cables outdoor, and riser cables Tight-Buffered: riser and plenum cables **Tight-Buffered:** riser and plenum cables Tight-Buffered: riser and plenum cables SC, FC, LC, ST® compatible, MTP SC, LC, FC, ST compatible, SC. LC. MTP® PRO connectors LC, MTP PRO connectors MTP PRO connectors PRO connectors 1.6. 2.0 mm 1.2, 1.6, 2.0 mm 1.2, 1.6, 2.0 mm 1.2, 1.6, 2.0 mm Yes Yes No Yes Yes Yes Yes, 1x2 only Yes Yes No No Yes Yes Yes Yes Yes N/A No Yes 1U and 2U only GR-449 Issue 3 compliant Scalable in features and function · Integrated fiber management Variety of field-termination options Base-8 and Base-12 fiber applications Industry-leading cable and jumper management Front-to-back jumper access Platinum interior color maximizes • Tip-to-tip solution for data centers and visibility storage area networks (SANs) Base-8 and Base-12 fiber applications Splitter compatible with Gen III and I S series Splice cassette for in-frame splicing in Ideal for structured Enclosed 4U housing option for 19-in or 23-in racks an easy-to-manage, compact footprint cabling in a data center Versatile cassettes/modules including staggered LC cassette for improved port access

Corning Optical Communications FTTP Selection Guide | CRR-630-AEN | Page 11



# Optical Splice Enclosures

When transitioning fiber and cable from outdoors to indoors, operators require a rugged enclosure that is optimized for quick re-entry and network expansion. The transition splice occurs in a different location from the optical fiber distribution frames to better manage the fiber and cable. Corning's optical splice enclosure (OSE) portfolio offers varying densities, scalability, and excellent fiber management with routing guide plates which organize and separate stored fiber and fiber entering splice trays. With options offering up to 6,912 ribbon and 5,184 single-fiber splice capacity, we can help support low- to high-density networks.

#### **Optical Splice Enclosures** CORNING Low Density 1,296 3,240 5,184 1.728 4,320 6,912 81.3 x 55.9 x 25.4 cm 114.3 x 55.9 x 33.0 cm 148.1 x 53.9 x 32.3 cm $(32.0 \times 22.0 \times 10.0 \text{ in})$ (45.0 x 22.0 x 13.0 in) (57 x 22.0 x 13 in) Up to 12 Up to 30 Up to 48 1-in OSE splice tray stacker 1-in OSE splice tray stacker 0.5-in splice tray stacker 0.5-in splice tray stacker 0.5-in splice tray stacker 0.2-in splice tray stacker 0.2-in slice tray tracker or 0.4-in splice tray stacker 0.4-in splice tray stacker 75 lbs (34.0 kg) 90 lbs (40.8 kg) 120 lbs (54.4 kg) Wall-mountable, rack 23-in Wall-mountable, rack 23-in Wall-mountable, rack 23-in Optical Splice Enclosure: 003-450-AEN Optical Splice Enclosure: 003-450-AEN Optical Splice Enclosure: 003-1032-AEN Cable Entry Kit: 003-354-AEN Cable Entry Kit: 003-354-AEN Cable Entry Kit: 003-1036-AEN Yes Yes No Yes Yes Yes Yes Yes Yes Equipment rooms, point of presence (POP) sites, utility Equipment rooms, point of presence (POP) sites, utility Equipment rooms, point of presence (POP) sites, utility sub-stations, basement cable vaults, and meet-me-rooms sub-stations, basement cable vaults, and meet-me-rooms sub-stations, basement cable vaults, and meet-me-rooms 0.090-in 5052-H32 aluminum sheet 0.090-in 5052-H32 aluminum sheet 0.090-in 5052-H32 aluminum sheet Cable entry plates allow various entry options including Cable entry plates allow various entry options including Cable entry plates allow various entry options including standard cable entry and mid-span cable access standard cable entry and mid-span cable access standard cable entry and mid-span cable access Provision for 28 cable entry positions, 14 each top & bottom Provision for 46 cable entry positions, 23 each on top & bottom Provision for 48 cable, all fed only from the top Horizontal pass-through ports provided near top and Horizontal pass-through ports provided near top and Horizontal pass-through ports provided near top and bottom of cabinet side bottom of cabinet side bottom of cabinet side





As the industry's leading supplier of cable assemblies, Corning's state-of-the-art manufacturing process ensures reliable connector performance with products that meet or exceed all industry standards for reflectance and insertion loss. Our ability to scale to meet your deployment needs is what sets us apart, along with the highest-quality fiber and factory-tested connectors. All assemblies undergo rigorous performance testing to ensure optimal quality in every connector.

Our new cable assembly configurator enables users to create part numbers while visually verifying different product attributes. This configurator provides reverse configuration features, realistic visualization, and dynamic specification sheet capabilities. Visit **www.corning.com/configurators/cab** to configure your next assembly.

### Assemblies










	Single-Fiber Assemblies	Duplex Assemblies	Duplex Zipcord Assemblies	Multifiber Assemblies
Subunit Size	1.2, 1.6, 2.0 mm	1.6, 2.0 mm	1.2, 1.6, 2.0 mm	1.2, 1.6, 2.0 mm
Fiber Size	250 μm (for the 1.2 mm) 900 μm (for the 1.6 and 2.0 mm)	250 μm (for the 1.2 mm) 900 μm (for the 1.6 and 2.0 mm)	900 μm	250 μm
Assembly Type	Jumpers, pigtails	Jumpers, pigtails	Jumpers, pigtails	Jumpers, pigtails, harnesses, trunks
Cable Design	Round	Round	Flat	Round
Application	Central office, headend, mobile switch center, remote	Central office, headend, mobile switch center	Central office, headend, mobile switch center, LAN	Central office, headend
Solution Compatibility	Centrix™ system, CCH, and Eclipse® hardware	EDGE™ and EDGE8® solutions	Centrix system, CCH, Eclipse hardware, EDGE and EDGE8 solutions	Centrix system, EDGE and EDGE8 solutions
Fiber Count	1	2	2	8, 12, 24, increments up to 1,728
Fiber Type	Bend-insensitive fibers Single-Mode: Corning® SMF-28® Ultra fiber Corning® ClearCurve® LBL or ClearCurve ZBL fibers	Bend-insensitive fibers Single-Mode: SMF-28 Ultra fiber Multimode: OM3, OM4, and OM5 fiber	Bend-insensitive fibers Single-Mode: SMF-28 Ultra fiber Multimode: OM3, OM4, and OM5 fiber	Bend-insensitive fibers Single-Mode: SMF-28 Ultra fiber Multimode: OM3, OM4, and OM5 fiber
Connector Types	SC APC, SC UPC, LC APC, LC UPC, FC APC, FC UPC, ST® compatible PC connectors	SC APC, SC UPC, LC APC, LC UPC, FC APC, FC UPC, ST compatible PC, uniboot (LC only) standard and lockable connectors	SC APC, SC UPC, LC APC, LC UPC, FC APC, FC UPC, ST compatible PC connectors	SC APC, SC UPC, LC APC, LC UPC, MTP® PRO connectors
Packaging	Bag, box, or reel Jumper in a box, figure-8 packaging	Bag, box, or reel Jumper in a box, figure-8 packaging	Bag, box, or reel Jumper in a box, figure-8 packaging	Bag, box, or reel
Quick Facts	Single-length management and simplified inventory with Jumper in a box for Centrix system-compatible assemblies (5 m)	<ul> <li>Quickly switch polarity in the field with LC uniboot connectors</li> <li>Simplified inventory management with Jumper in a box</li> </ul>	<ul> <li>Easily separate connector ends in the field for simplified routing</li> <li>Simplified inventory management with Jumper in a box</li> </ul>	<ul> <li>High-performance and quick connectivity with MTP PRO connector-enabled assemblies</li> <li>Manage polarity (type A or B) in conjunction with Corning's universal polarity EDGE systems</li> </ul>





We invented the first low-loss optical fiber over 51 years ago, igniting the critical spark that began a communications revolution. And today, after recently delivering our 1 billionth kilometer of fiber, we continue to lead the industry in product quality and innovation. Corning cables with binderless\* FastAccess\* technology feature a groundbreaking innovation in cable design that eliminates the use of binder and waterblocking yarns and waterblocking tapes, resulting in significant time-savings. Corning FastAccess cables can be accessed up to 70% faster and reduce the risk of buffer tube damage. With designs for every environment, our innovative cables solve your unique application challenges, from congested duct space and environmental extremes, to mechanical forces and cable entry concerns.

\*Corning's proprietary binderless FastAccess® technology refers to the combination of a Corning FastAccess technology jacket with an innovative technology used to bind cable construction through the manufacturing process, eliminating the use of binder yarns and waterblocking tapes.





	Loose Tul	be Cables	Micro	Cables
CORNING				
	ALTOS® Loose Tube Cable	SOLO® All-Dielectric Self-Supporting (ADSS) Cable	MiniXtend® Cable	MiniXtend HD Cable
Fiber Size	250 μm	250 μm	250 μm	200 μm
Splicer Compatibility	Single-fiber splicers	Single-fiber splicers	Single-fiber splicers	Single-fiber splicers
FastAccess® Technology	Yes, up to 288 F in dielectric; up to 72 F in armored; binderless* FastAccess technology up to 72 F (dielectric only)	No	Yes, with binderless* FastAccess technology	Yes, with binderless* FastAccess technology
Water Blocking Technology	Gel-free and Gel-filled	Gel-filled	Gel-filled	Gel-filled
Environment	Aerial lashed, duct, direct-buried (armored recommended for direct-buried and toning)	Aerial self-supporting, best near power lines or for long spans	Microduct	Microduct
Duct Requirements (inner diameter)	Dielectric and Lite armored cable: 1.25-in duct up to 432 fibers	Aerial only	8 mm microduct: 12-96 fibers 10 mm microduct: 144 fibers	12 mm microduct: 288 fibers 14 mm microduct: 432 fibers
Armor Available	Yes	N/A	No, armored and toneable microducts are available from microduct vendors	No, armored and toneable microducts are available from microduct vendors
Flame-Rated Version	FREEDM® indoor/outdoor cable, riser LSZH™ cable	No, outdoor only	FREEDM indoor/outdoor cable	No
Fiber Count	12-432	12-288	12-288	144-432
Quick Facts	Most widely deployed cable design globally	<ul> <li>Ideal when no strand is available to lash to and new strand is cost prohibitive</li> <li>Designed for deploying in the power supply zone</li> </ul>	FastAccess technology enables up to 70% faster cable access and 80% lower installation cost vs. standard cable jackets, reduces risk of damage to buffer tubes and fibers	Utilizes 200 µm single-mode optical fiber to achieve the most dense cable

<sup>\*</sup>Corning's proprietary binderless FastAccess® technology refers to the combination of a Corning FastAccess technology jacket with an innovative technology used to bind cable construction through the manufacturing process, eliminating the use of binder yarns and waterblocking tapes.



#### **Ribbon Cables CORNING** Corning® RocketRibbon® Cable SST-Ribbon™ Cable RPX® Gel-Free Ribbon Cable **Fiber Size** 250 μm 250 μm 200\* or 250 μm **Splicer Compatibility** Mass fusion splicers Mass fusion splicers Mass fusion splicers FastAccess® Technology No No Yes, except 1,728 and 3,456 **Water Blocking Technology** Gel-free Gel-free Gel-free Outdoor aerial, duct and direct buried; also typically Aerial lashed, duct, direct-buried (armored Aerial lashed, duct, direct-buried in distribution segment as part of FlexNAP™ terminal **Environment** recommended for direct-buried and toning) (armored recommended for direct-buried and toning) distribution system 144-864: 1.25-in duct 1.0 to 1.25-in duct: up to 144 fibers **Duct Requirements** 1.25-in duct: up to 864 fibers 1,728: 1.5-in duct 3.456 or 2.0-in duct **Armor Available** Yes No Yes, for less than or equal to 1,728 FREEDM indoor/outdoor cable, Flame-Rated Version FREEDM® indoor/outdoor cable, riser or plenum No LSZH™/riser (dual listing) coming soon 12-864 24-144 **Fiber Count** 144-864; 1,728; or 3,456\* Utilizes conventional 12- or 24-fiber ribbons packaged in Utilizes 6- x 4-fiber splittable 24-fiber ribbons packaged in a routable sleeve or subunit design that offers ease of Ribbon stack comprised of a combination of 12-, 24-, a rugged and compact design suitable for short-span ADSS **Quick Facts** installation coupled with innovative ribbon protection. and 36-fiber ribbons helically stranded in a central tube applications and FlexNAP terminal distribution system. Offers up to twice as much fiber per duct and 60% faster Available in all-dielectric and toneable designs



cable access than existing solutions

<sup>\*200</sup> µm fiber optional



# Local Convergence Point

The network you build today will serve your customers for many years, so we've designed our family of cabinets to serve them well. These cabinets, the cornerstone of our FTTH portfolio, enable quick subscriber turn-up and error-free, long-term management of your climbing take rates. See the following options to find your ideal balance of size, density, and features. All cabinets incorporate our innovative cable routing and splitter storage.

#### **Outdoor LCPs** CORNING Splitter Cabinet, MAC Series Splitter Cabinet, PAC Series Architecture Centralized Centralized Centralized 1,152 distribution fibers 72, 144, 288, 432, 576, 864 fibers 144, 288, 432, 576, 864 fibers Capacity **Prestubbed Feeder** Use of stubbed and splice on frame applications is ALTOS® gel-free cable, SST-Ribbon™ gel-free cable ALTOS gel-free cable, SST-Ribbon gel-free cable supported by use of Centrix housings Distribution Stub(s) Yes Ribbon dielectric or armored Note: Stubbed distribution housings are supported 288 & 576: Pad or Pole; **Mounting Options** Pad or pole Inside various industry copper cabinets 864: Pad None (cross-connect), dual 1x4, dual 1x8, dual 1x16, **Splitter** Dual 1x4, dual 1x8, dual 1x16, 1x32 or 1x64 Dual 1x4, dual 1x8, dual 1x16,1x16, 1x32, or 1x64 1x16, 1x32, or 1x64 **xWDM Capability** No Yes Yes Splice No No No **Splitter Compatibility** LS or RM series splitters LS or RM series splitters LS or FOS **Pass-Through Capability** Yes Yes Yes

#### **Outdoor LCPs Indoor LCPs CORNING** Local Convergence Cabinet, Local Convergence Cabinet, Enclosure (LCPE) Indoor Gen III Series Indoor LS Series Indoor CE Series Architecture Centralized Centralized, distributed Centralized, distributed Centralized, distributed Centralized, distributed 72, 96, 144 fibers (SC APC); 72, 96, 144, 288, 432, 576, 32 fibers Capacity 144, 288, 432 fibers 144, 288, 432, 576, 864 fibers 144 and 288 fibers (LC APC) 864 fibers Prestubbed LT to ALTOS® cable: SST-Ribbon cable. FREEDM ribbon riser cable. FREEDM ribbon riser cable. Prestubbed Feeder four 12-fiber tails or one ALTOS cable, SST-Ribbon™ cable FREEDM® ribbon riser cable, FREEDM loose tube cable FREEDM loose tube cable 48-fiber tail ALTOS riser cable Accomplished with RPDpass® Distribution Stub(s) Yes Yes Yes Yes riser assemblies or direct drops Aerial strand and pole-mount, Aerial strand and pole-mount, Wall- or rack-mount **Mounting Options** Wall- or rack-mount Wall- or rack-mount pedestal, handhole, manhole pedestal, handhole, manhole Dual 1x4, dual 1x8, Dual 1x4, dual 1x8, Dual 1x4, dual 1x8, **Splitter** 1x32 Dual 1x8, dual 1x16, 1x32, or 1x64 dual 1x16, or 1x32 dual 1x16, 1x32, or 1x64 dual 1x16, or 1x32 **xWDM Capability** Yes Yes Yes Yes Yes Splice No Yes, splice option available Yes Yes Yes SC APC use LCPE series **Splitter Compatibility** Splitter is factory installed LC APC use RM series LS/Gen III series splitters Gen III series splitters LS series splitters WDM LCPE Splitters **Pass-Through Capability** Yes Yes No





# Closures and Terminals

Whether your FTTH network design has closures in a buried or aerial environment, one thing remains the same: you need assured environmental protection and quick, incremental subscriber drops. From our experience in the field, we know that not all closures are the same. Our preconnectorized terminals are thoughtfully designed to incorporate individual strain-relief, sealing of all cables, and quick-release clamps for easy re-entry. With our expanded solution portfolio, we can help you choose the one that's best for your deployment from the following tables.

To learn more, visit us at www.corning.com/cable-and-closure-solutions

### **Below-Grade Closures**









	2178 Series Closures	SCF Series Closures	SCF Series Closures UCA Series Closures	
Best Fit Cable Type*	Ribbon/Single fiber	Ribbon/Single fiber	Loose tube	Loose tube/Ribbon
	Vault (FR), handhole, strand, pole	Handhole, strand, pole	Strand, pole, pedestal, façade	Strand, handhole, pole
Single-Fiber Splices – Loose Tube	XSB: 48, XLB 96 S: 96 L: 288 XL: 576	72, 192, 384, 576	36	FDC08M-96 FDC08S-192 FDC10S-576 FDC12S-720
Mass Fusion Splices – Ribbon	XSB: 166, XLB 288 S: 288 L: 864 XL: 1,728 or 3,456	1,152 or 1,728	144 fibers (12 ribbons)	FDC08M-288 FDC08S-576 FDC10S-864 FDC12S-2880
	Mechanical	Mechanical	Mechanical	Mechanical
Doubles as Terminal	Yes, small sizes support spliced drops	No	Yes, spliced or via ports	Yes, spliced or via ports
Pre-term Compatibility	None, splice only	None, splice only	Hardened OptiTip® or OptiTap® connectors	Non-hardened, SC and LC Hardened OptiTip or OptiTap connectors
Number of Distribution/ Drop Cables	Expandable kits available; port counts vary	3, 4, 6	4	Based on type of base and grommet in the ECAM
Maximum Number of Cable Ports	XS: 3 Butt only S: 2 per side L: 2 per side XL: 4 per side	5, 6, 8	20	Based on the base type 8(8M-A), 3(8S-B), 5(8S-C), 8(8S-C) 7(10S), 5(12S)
Cable Entry Style	In-line, butt	Butt	In-line, butt	Butt
Slack	Yes	Yes	Yes	Yes
Accommodates Splitters and xWDM	Yes	Yes	Yes	Yes
IEC/GR or Specific Attribute	GR-771	GR-771	GR-771	GR-771


<sup>\*</sup>All closures are compatible with multiple cable designs. Visit https://www.corning.com/optical-communications/worldwide/en/home/products/fiber-closures.html.





	Below-Grade Closures	Above-Gra	de Closures
CORNING			
	BPEO Series Closures	SCA Series Closures	SLiC <sup>®</sup> Fiber Aerial Closures
Installation Environment	Handhole, pole, façade	Strand	Strand
Single-Fiber Splices – Loose Tube	BPEO Size 0: 48 Single Fiber BPEO Size 1: (84/144 Single Fiber) BPEO Size 1.5: 144 Single Fiber BPEO Size 2: 336 Single Fiber BPEO Size 3: 576 Single Fiber	72, 144	Model 533-72 fibers Model 547-72 fibers Model 733-144 fibers
Mass Fusion Splices – Ribbon	N/A	144 and 216	Model 533-432 fibers Model 547-432 fibers Model 733-864 fibers
Sealing Type	Mechanical	Gel	Free-breathing
Doubles as Terminal	Yes	Yes	Yes, with OptiTap®, ECAM, or direct splice
Connector Type	None or non-hardened SC, or OptiTap Pushlok™	Splice, SC, or OptiTap connectors	Splice, SC, or OptiTap connectors
Number of Distribution/ Drop Cables	Up to 25, 4 OptiTap, 12 Pushlok	6, 16	24
Maximum Number of Cable Ports	Up to 29	22	28
Cable Entry Style	Butt	In-line, butt	In-line, butt
Slack	Yes	Yes	Yes
Accommodates Splitters, xWDM and Other Optical Devices	Yes, including distributed tap splitters	Yes	Yes
Industry Ratings	5 meters 7 days	Telcordia TR TSY-000949 and GR-771 requirements	GR-771 (aerial)






Save time and money with our FlexNAP™ system, a pre-engineered factory-terminated network access point integrated into fiber optic distribution cables. Designed for FTTH networks, the factory-tested and factory-sealed system deploys up to 50% faster than traditional deployment methods by eliminating costly field splices. The FlexNAP system simplifies installation by using the same methods as bulk cable while leveraging the speed of preconnectivity. Depending on your network architecture, either the FlexNAP standard, single-fiber, or multiuse system will be your choice for this technician-friendly FTTH innovation. Trust in a technology that's helped operators pass more than 30 million premises and counting.

To learn more, visit us at www.corning.com/flexnap

		FlexNAP <sup>™</sup> System	
CORNING		Oi Oi	
	FlexNAP™ Standard System	FlexNAP Single-Fiber System	FlexNAP Multiuse System
Architecture	Centralized, home run	Distributed	Combined home run, centralized, distributed
Maximum Fiber Count	ALTOS® loose tube cable (dielectric, armored, or figure-8): 432 fibers with 204 terminated remainder expressed  RPX® ribbon cable (dielectric or toneable): 144 fibers	ALTOS loose tube cable (dielectric or armored): 432 fibers with 204 terminated remainder expressed RPX ribbon cable (dielectric or toneable): 144 fibers SST-Drop™ cable (dielectric): 12 fibers	ALTOS loose tube cable (dielectric or armored): 432 fibers with 204 terminated remainder expressed RPX ribbon cable (dielectric or toneable): 144 fibers
Aerial Self-Supporting Cable	Yes, with RPX ribbon or ALTOS figure-8 cable	Yes, with RPX ribbon cable or SST-Drop cable	Yes, with RPX ribbon cable
Buried Environment	Loose tube: 1.25-in duct up to 72 fibers dielectric, 2-in duct up to 216-fiber dielectric, or 72-fiber armored cable RPX ribbon cable: 2-in duct	Loose tube: 1.25-in duct up to 72 fibers dielectric, 2-in duct up to 216-fiber dielectric, or 72-fiber armored cable RPX ribbon cable: 2-in duct SST-Drop cable (dielectric): 1.25-in duct	RPX ribbon cable: 2-in duct
Maximum Tethers per Tap	2, dual tap dual tether option available to access 48-fibers max per location	2	
Multifiber Connector Tether Options	<b>Loose tube:</b> 2, 4, 6, 8, or 12 <b>RPX ribbon cable:</b> 4, 8, or 12	N/A	<b>Loose tube:</b> 2, 4, 6, 8, or 12 <b>RPX ribbon cable:</b> 4, 8, or 12
Single-Fiber Connector Tether Options	N/A	Loose tube: 1 SST-Drop cable: 1 Tethers with more than 1 fiber have secondary furcation point	Loose tube: 1, 2, or 4 RPX ribbon: 4 Tethers with more than 1 fiber have secondary furcation point
Supports Preterm Laterals	Yes, maximum 72 fiber per lateral	Yes, maximum 48 fiber per lateral	Yes, maximum 48 fiber per lateral
Pretermination Possible at Cabinet	No	No	Yes, maximum 48 fiber via dual tether dual tap with pretermination-enabled cabinet
OSP Terminal Compatibility	Supports Legacy Evolv™ terminals	Supports 1:4 and 1:8 stubless splitter Evolv terminals or direct connect to drops	Supports Evolv terminals
MDU Terminal Compatibility	Supports multifiber connector-enabled MDU and LPT terminals	Supports single-fiber connector-enabled splitter MDU and LPT terminals	Supports connector-enabled MDU and LPT terminals



## FlexNAP™ systems support all architectures





## **Outside Plant Terminals**

Specifically designed for outside plant (OSP) fiber access networks, our multiport family delivers fully sealed environmental protection and fast, easy incremental connection for increased deployment velocity. For the greatest deployment acceleration, you can pair connector-enabled terminals with our FlexNAP<sup>™</sup> system. Another best practice is to consolidate cable access points by routing several terminal stubs to a single-splice location, increasing workforce efficiency and reducing the total connection time for subscribers.

Through our extensive FTTH experience, we've designed these OSP terminals with flexible form factors and integrated splitters to adapt to your individual network. Look at the following table to see which combination of features is right for you.

To learn more, visit us at www.corning.com/go

### Subscriber Terminals











					111 100
	MultiPort (MOB)	MultiPort Flex Stubbed (MOF)	MultiPort (MTB)	MultiPort Flex (MPF)	Evolv™ Terminal (DM/DF)
Architecture	Centralized	Centralized	Centralized	Centralized	Centralized
Drop Capacity	2, 4, 6, 8, 12 ports	4, 8, 12 ports	2, 4, 6, 8, 12 ports	4, 8, 12 ports	2, 4, 6, 8, 12, 16 ports
Input Cable	SST-Drop™ cable (toneable or dielectric) MiniXtend® cable	SST-Drop cable (toneable or dielectric) 4.8 mm round drop (legs)	RPX® ribbon cable < 18 ft (toneable or dielectric) 4.8 mm round drop (legs) or SST-Drop cable > 18 ft (toneable or dielectric)	4.8 mm round drop (legs)	SST-Drop cable or (toneable or dielectric) MiniXtend Cable or Long-Span SST-Drop
Input Connector	None (stubbed)	None (stubbed)	OptiTip® multifiber hardened connector	OptiTip multifiber hardened connector	None (DM); OptiTip multifiber hardened connector (DF)
Splitter	No	No	No	No	No
Low Profile	No	Yes	No	Yes	Yes
FlexNAP™ System Compatible	No	No	Yes	Yes	Yes
Expansion Port	No	No	No	No	No
Port Type	OptiTap® adapter	OptiTap adapter	OptiTap adapter	OptiTap adapter	Pushlok™ single-fiber adapter

### **Splitter Terminals**













	MultiPort Splitter (MOS/MTS)	MultiPort Splitter Stubless (MTS)	MultiPort Flex Splitter (MSF)	MultiPort Distributed TAP (MDT)	Evolv™ Splitter Terminal (DS)	Evolv Distributed TAP (DT)
Architecture	Distributed	Distributed	Distributed	Distributed TAP	Distributed	Distributed TAP
Drop Capacity	4, 8 ports	4, 8 ports	4, 8 ports	2, 4, 8 ports	2, 4, 8, 16 ports	2, 4, 8 ports
Input Cable	SST-Drop™ cable (tone- able or dielectric)	None; OptiTap® drop assembly serves as input cable	4.8 mm round drop	None	None; Pushlok™ drop assembly serves as input cable	None, Pushlok drop assembly serves as input cable
Input Connector	None; (stubbed) or OptiTap connector (male) or OptiTip® multifiber hardened connector (with expansion port only)	OptiTap single-fiber hardened connector (female)	OptiTap single-fiber hardened connector (female)	OptiTap single-fiber hardened connector (female)	Pushlok single-fiber	Pushlok single-fiber
Splitter	1x4 or 1x8	1x4 or 1x8	1x2, 1x4, or 1x8	One uneven 1x2 (90/10 to 60/40 available) with one standard 1x2, 1x4 or 1x8	1x2 , 1x4, 1x8, or 1x16	One uneven 1x2 (90/10 to 60/40 available) with one standard 1x2, 1x4 or 1x8
Low Profile	No	No	Yes	No	Yes	Yes
FlexNAP™ System Compatible	No	Yes	Yes	Yes, FlexNAP single-fiber system as feeder trunk	No	No
Expansion Port	Configurable	No	No	Yes	No	Yes
Port Type	OptiTap adapter	OptiTap adapter	OptiTap adapter	OptiTap adapter	Pushlok single-fiber	Pushlok single-fiber

#### **Distribution Terminals** CORNING UltraNAP™ 4-Port Terminal UltraNAP 6-Port Terminal MF2 MultiPort Terminal MF4 MultiPort Terminal MF12 MultiPort Terminal (B1, S1) (B1, S1) Architecture Centralized Centralized, home run Centralized, home run Centralized, home run Centralized 12-fiber capacity: 12-fiber capacity: 4-24 fiber capacity: 4-48 fiber capacity: 48-144 fiber capacity: Four OptiTap® ports Six OptiTap ports 2, 3, 4, 6, 8, or 12 2, 3, 4, 6, 8, or 12 2, 3, 4, 6, 8, or 12 **Drop Capacity** with two 4-fiber OptiTip® with one 6-fiber OptiTip 2-fiber OptiTip ports 4-fiber OptiTip ports 12-fiber OptiTip ports expansion ports expansion port SST-Drop cable SST-Drop cable SST-Drop™ cable ALTOS cable SST-Drop cable (toneable or dielectric) (toneable or dielectric) **Input Cable** (toneable or dielectric) (toneable or dielectric) MiniXtend® cable MiniXtend cable RPX® ribbon cable ALTOS® cable ALTOS cable None (stubbed) None (stubbed) None (stubbed) None (stubbed) OptiTip multifiber hardened **Input Connector** OptiTip multifiber hardened None (stubbed) OptiTip multifiber hardened OptiTip multifiber hardened connector (6 ports/12-fiber connector (3 ports/12-fiber connector connector maximum for preconnectorized) maximum for preconnectorized) **Splitter** No No No No No **Low Profile** No No No No No FlexNAP™ System Yes Yes Yes Yes No Compatible **Expansion Port** Yes Yes No No No

OptiTip adapter

OptiTap & OptiTip adapter

OptiTap & OptTip adapter

**Port Type** 

OptiTip adapter

OptiTip adapter



Whether you're servicing a business or a residence, there's no one-size-fits-all answer for your multidwelling or multitenant needs. You need a customized solution and a collaborator with the expertise to simplify your challenges, so you can focus on delivering the services and applications that your subscribers expect. Other variables like aesthetics, labor skill level, and rights-of-way access will factor into your architecture and product selection. Choose a supplier that knows your environment and has manufacturing expertise that can help you choose flexible, simplified product sets. What you will find on the following pages are a range of solutions that address the wide variety of environments you may encounter in the field, backed by the expertise we've gained in more than 15 years of global deployments.

To learn more, visit us at www.corning.com/mdu

### Multidwelling Unit Terminals











	MDU Terminal	MDU Splitter Terminal	Zone Terminal	Low-Profile Terminal (LPT)	Low-Profile Terminal (LPT) with Splitters
Architecture	Centralized, home run	Centralized, distributed	Centralized	Centralized, home run	Distributed
Environment	Indoor/outdoor	Indoor/outdoor	Indoor/outdoor	Indoor/outdoor	Outdoor
Capacity	6, 12, 24, 36, 48 fibers	4, 8, 16, or 32 fibers	72, 96, 144, 216, 288 fibers	4, 6, 8, 12 fibers	4, 8 fibers
Prestubbed Feeder	OptiTip® stub, MTP® PRO connector, ALTOS®, SST-Ribbon™, and FREEDM® loose tube indoor/ outdoor cables	FREEDM loose tube indoor/ outdoor cable, 4 or 12 fibers	FREEDM loose tube or FREEDM Ribbon (ribbon stub end can be connectorized with non-pinned MTPs)	OptiTip stub, MTP connector enabled: RPDpass riser cable assembly (indoor only) FREEDM or SST	No; OptiTap® or SC APC options
Compatible Solutions	FlexNAP™ system with OptiTip stubs or adapter ports; RPDpass® riser assemblies	No	RPD pass riser cable assembly	FlexNAP system with OptiTip stubs RPDpass riser assemblies	FlexNAP system with OptiTap connector
Drop	Ultra bend-insensitive single-mode drop cable (2.9 to 4.8 mm)	Ultra bend-insensitive single-mode drop cable (2.9 to 4.8 mm)	N/A when used as a basement terminal, Corning® Clear Track Hallway-enabled with MTP connectors when used as a zone terminal	Ultra bend-insensitive single-mode drop cable (2.9 to 4.8 mm)	Ultra bend-insensitive single-mode drop cable (2.9 to 4.8 mm)
Splitter	No	1x32 or dual 1x4, dual 1x8, dual 1x16	No	No	1x4, dual 1x4, or 1x8
Slack	Yes, optional rear metal housing or plastic skirt for additional storage	Yes, optional rear metal housing or plastic skirt for additional storage	Yes, optional rear metal housing or plastic skirt for additional storage	Yes, optional rear plastic housing or plastic skirt for additional storage	Yes, optional rear plastic housing or plastic skirt for additional storage
Splice	Yes	Yes	No	No	No, OptiTap connector input

### **MDU Terminals**

### Network Interface Devices (NIDs)













	•		E3 🖺 E3			
	Fiber Distribution Terminal (PBOC Series)	Riser Distribution Terminal (RTW or RTC)	Integrated Fiber NID	Fiber Transition Housing (FTH-602)	Transition Housing (FTH-76S)	Fiber Transition Housing (FTH-NG1)
Architecture	Centralized, distributed, or home run	Centralized, home run	Centralized, home run	All	All	All
Environment	Indoor/outdoor	Indoor	Outdoor	Indoor/outdoor	Indoor/outdoor	Indoor/outdoor
Capacity	Up to 10 SC or 20 LC, LC duplex only	12, 24 fibers (by adding 12-F SC modules) or up to 36-F using MTP® adapter panel	1 or 2 fibers	1-6 fibers	1-6 fibers (spliced) 1-2 fibers (connectorized)	1-24 fibers (connectorized)
Prestubbed Feeder	N/A	MTP-enabled	N/A	SC UPC/APC LC UPC/APC	SC APC OptiTap® adapter (1 fiber only)	SC UPC/APC LC UPC/APC
Compatible Solutions	No	RPDpass® and Clear Track solutions	No	Field-installable connectors	Field-installable connectors	Field-installable connectors
Drop	Ultra bend-insensitive single-mode drop cable, SST-Drop™ or ROC™ drop cables	2.9 mm compact, 4.8 mm rugged, Corning® Clear Track Hallway, RPDpass horizontal	Up to 4.8 mm drop cables	Up to 4.8 mm drop cables	Up to 4.8 mm drop cables	Up to 4.8 mm drop cables
Splitter	Yes, up to 1x8 in SC or 16 in LC duplex	No	No	No	No	No
Slack	No	Yes	Yes, up to 35 ft of 4.8 mm	3 m	10 m	Repair loop only
Splice	Yes, to pigtails for preconnectorized drops or full splice directly to drops	No	Yes, to pigtails for preconnectorized drops or full splice directly to drops	Mechanical, fusion	Fusion	No splicing



# Drop Assemblies

To reduce the cost and time of deploying drop cables in your optical access network, we factory terminate our drops with either SC APC or environmentally sealed Pushlok connectors. These innovative single-fiber drop cable assemblies enable quick, highly reliable customer connections – without field splicing. Available on a wide variety of cables, you can choose a design that's right for your application. Determine which product best fits your needs using the following tables.

#### **Outdoor Drops** CORNING ROC™ Drop 900 SST-Drop™ SST-Drop In-Line Cable SST-Drop Indoor/ Drop Cable Assembly Assembly, Female OptiTap® Connector OptiTap to SC APC assembly, OptiTap pigtail, SC APC jumper, or Pushlok™ OptiTap to SC APC assembly, OptiTap Female OptiTap pigtail or female-to-male OptiTap to SC APC assembly or OptiTap Connectorized to SC APC assembly or Pushlok pigtail or SC APC to SC APC jumper OptiTap assembly pigtail (2-fiber only available as pigtail) single-fiber pigtail Toneable/Dielectric Both Both Both Both **Buried/Aerial** Both Both Both Both **Fiber Subunit** 900 μm 250 μm 900 μm 250 μm FastAccess® Technology Yes No No No Flat/Round Cable Flat Flat Flat Flat Indoor/outdoor Indoor/Outdoor Outdoor Outdoor Outdoor 1-2 **Fiber Count** 1 1-2 Bend-insensitive Single-mode fiber Single-mode fiber Single-mode fiber Fiber Type single-mode fiber **Pulling Grip** No Available Available Available for 1-fiber assemblies Compact outdoor drop allows for more Ideal to branch off multiports and Suited for applications where two Robust flat drop cable for self-supporting **Quick Facts** slack to be managed at subscriber position at lot lines between subscriber services (e.g., business and residential) or direct-buried applications exist at the same subscriber location premise premise

### **Indoor/Outdoor Drops** CORNING Evolv™ Round ROC™ Drop Cable Corning® ClearCurve® DualDrop™ Assemblies with Pushlok™ Cable Assembly Connectorized: Pushlok™ single-fiber to Pushlok Unterminated: SC APC or SC SC APC or SC UPC SC APC or SC UPC single-fiber, Pushlok single-fiber Connectorized OptiTap pigtail only APC patch cord to SC APC (jumper or pigtail) (jumper or pigtail) to SC APC Simplex, and Pushlok single-fiber pigtail single-fiber pigtail Toneable/Dielectric Dielectric Dielectric Dielectric Dielectric Dielectric **Buried/Aerial** Both Both Aerial No Both **Fiber Subunit** 900 μm 900 μm 900 μm 900 μm 900 μm FastAccess® Technology No Yes Yes No No Flat/Round Cable Round Round Round Round Round Indoor/outdoor Indoor/outdoor Indoor/outdoor Indoor/outdoor Indoor/outdoor Indoor/Outdoor **Fiber Count** 1 Bend-insensitive Ultra bend-insensitive Ultra bend-insensitive Ultra bend-insensitive Single-mode fiber Fiber Type or bend-insensitive fiber single-mode fiber single-mode fiber or bend-insensitive fiber **Pulling Grip** No Available Available No Optimized for running Eliminate transition Less visible, resulting in inconspicuously under carpet Self-bend-limiting jacket allows housing by removing outdoor an aesthetically pleasing look and along door frames or **Quick Facts** Ideal for pull and/or jet installs for widest variation of installajacket and route directly to for both homeowners and molding. Also suitable for tion methods including stapling subscriber ONT indoors raceway and microduct property owners installations



### **Indoor Drops** In-Living Unit (ILU) CORNING RPDpass® Corning® Clear Track RPDpass Drop SC APC Shuttered Jumper Riser Cable Assembly Micro-Module Connectorized MTP® PRO connector jumper SC APC pigtail or MTP PRO pigtail SC APC pigtail or MTP PRO pigtail SC APC shuttered 6-fiber: 4.8 mm Cable: 3 mm **Outer Dimensions** 8-fiber: 5.2 mm 1.8 mm 3.0 mm Grip: 18 mm (0.72 in) 12-fiber: 6.5 mm **Fiber Size** 900 µm 900 μm 900 μm 250 μm 1.65 mm subunits Cable Design Micro-Module Micro-Module Round bundled (no outer jacket) Installation Conduit Conduit Wall/trim or conduit N/A Indoor/Outdoor Indoor only Indoor only Indoor only Indoor only 12 or 24 6, 8, or 12 12 **Fiber Count** Ultra bend-insensitive fiber Ultra bend-insensitive fiber Fiber Type Ultra bend-insensitive fiber Ultra bend-insensitive fiber Collapsible plastic reel Corrugated plastic reel Reel **Packaging** Bag Pulling Grip Standard Available Standard No Can be easily laid and captured within Binderless bundled construction allows Suited for larger MDUs where riser the Clear Track Hallway Fiber Pathway Ideal connection from low-profile wall **Quick Facts** for quick access to individual subscriber conduit space may be limited with the Clear Track Hallway Fiber space with visual connection reference subunits for termination

Installation Tool



Whether you're taking fiber to the living unit or fiber all the way into a living unit, Corning's variety of small transition boxes and outlets provide the optimal transition point for a variety of applications. With a number of different connector styles and mounting options, each solution offers a custom fit for your fiber deployment. All products are easy to deploy and can be used in both single-family and multifamily unit installations. As fiber progresses closer to subscribers, these transition points will become increasingly important in your network.

To learn more, visit us at www.corning.com/cleartrack

	Distribution		In-Living Unit (ILU)					
CORNING						The state of the s		
	Small Point-of- Entry (POE) Box	Micro POE Box	Low-Profile Wall Plate	Wall Outlet (WLL)	Shuttered Wall Terminal (SWT)	Shuttered Wall Box (SWB)	Fiber Point-of-Entry Sliding Wall Cover	
Environment	Hallway	Hallway	In-living unit	In-living unit	In-living unit	In-living unit	In-living unit	
Installation	N/A	N/A	Wall-mountable or outlet	Outlet (flush)	Wall-mountable	Wall-mountable or outlet (cover)	Wall-mountable	
Capacity	1SC adapter inside	Pass-through	1 port	2 keystone ports	4 ports	2 keystone ports	2 ports	
Connectivity Type	SC	N/A	SC	Shuttered SC compatible with alternative keystone ports (LC, CAT x)	SC, LC	Shuttered SC compatible with alternative keystone ports (LC, CAT x)	SC	
Cable Compatibility	1.8/2.0 Micro Module and 900 µm Clear Fiber	900 μm	900 μm	All indoor drops	All indoor drops	All indoor drops	All indoor drops up to 4.8 mm	
Slack	3 ft of both fiber types above (6 ft in total)	N/A	6 ft of 900 μm	N/A	1-3 ft, depending on cable size	1-3 ft, depending on cable size	3 ft of 2.9 mm	
Quick Facts	Supports mid-span access to separate and terminate individual subscriber fiber, allowing remaining fibers to pass through	Conceals the hole from hallway into subscriber living unit while protecting subscriber drop	Integrated shuttered SC APC port with visual indicator ensures safe subscriber connect- ions with SC APC shuttered jumper	Suitable for greenfield construction and compatible with standard wall junction boxes	Surface-mount configurable terminal to support up to 4 ports, flexible for business and residential environments	Surface-mount subscriber demarcation leveraging shuttered adapters	Surface-mount subscriber demarcation compatible with rugged drops up to 4.9 mm	



# **Bulk Drop Cables**

Engineered to withstand demanding conditions, from environmental extremes to mechanical forces, our drop cables can be strung aerially along telephone poles, installed inside underground ducts, or buried directly below ground. We protect the integrity of our optical fibers with rugged constructions and resistance to ultraviolet light and temperature fluctuations. However you plan to deploy your subscriber drops, we've included a cable design for you on the next page.

	Flat Drop Cables							
CORNING					day			
	SST-Drop™ Cables	ROC™ Drop 900 Cables	SST-Drop Indoor/Outdoor Cables	Long-Span Drop Cables	Clear Drop Cables			
Toneable/Dielectric	Both	Both	Both	Dielectric	Dielectric			
Cable Size	8.1 x 4.5 mm	6.6 x 3.0 mm	8.1 x 4.5 mm	12.7 x 4.4 mm	2.5 x 4 mm			
Fiber Size	250 μm	900 μm	900 μm	250 μm	900 μm			
FastAccess® Technology	Yes	Yes	Yes	No	Yes			
Installation	Aerial/buried (toneable recommended for buried)	Aerial/buried (toneable recommended for buried)	Aerial/buried (toneable recommended for buried)	Aerial (designed specifically for long-span aerial applications in NESC medium-to-heavy conditions)	Aerial/buried (can be adhered to home using staples or clips. Jacket is removed before indoor installation)			
Indoor/Outdoor	Outdoor	Outdoor	Indoor/outdoor	Outdoor	Indoor/outdoor			
Fiber Count	1-24	1	1-2	1-12	1			
Fiber Type	Single-mode fiber	Single-mode fiber, bend-insensitive single-mode fibers	Bend-insensitive single-mode or ultra bend-insensitive single-mode fiber	Bend-improved single-mode fiber	Bend-insensitive or ultra bend-insensitive single-mode fiber			
Option to Preconnectorize	Yes, one or both ends with OptiTap® or SC APC connectors	Yes, one or both ends with OptiTap or SC APC connectors	Yes, one or both ends with OptiTap or SC APC connectors	No	Yes, one or both ends with SC APC connectors			
Packaging	Reel in a box	Reel in a box	Bulk or reel in a box	32-in or 42-in reel	Bulk, reel in a box, or bag			
Quick Facts	Offers exceptional crush resistance in an easy-access, single-tube design	Reduced OD increases flexibility and improves slack storage as compared to standard flat drop cables	Eliminates indoor ONT transitions with a flame-rated indoor subunit with OptiTap or SC APC connectors	<ul> <li>Enables span lengths up to 500 ft with no support or messenger wire required</li> <li>Compatible with OptiSnap® and OptiTap field-installable connectors</li> </ul>	Clear Drop eliminates the need for termination hardware to transition from the outdoor environment to an indoor terminal, with a clear internal subunit for nearly invisible routing in living units			



	Round Drop Cables			Corning <sup>®</sup> Clear Track Fiber			
CORNING							
	Jetted Round Drop Cables	Corning® ClearCurve® Rugged Drop Cables	ClearCurve Compact Drop Cables	Corning® Clear Track 900 µm Clear Fiber	Clear Track Quad with Four 900 µm Clear Fibers	Clear Track Hallway with 12-Fiber Micro-Module	
Toneable/Dielectric	Dielectric	Dielectric	Dielectric	N/A	N/A	N/A	
Fiber Size	900 μm	900 μm	900 μm	900 μm	900 μm	1.8 mm (diameter size for 8- and 12-fiber counts), 2 mm (diameter size for 16-fiber counts)	
FastAccess® Technology	Yes	No	No	No	No	No	
Installation	Aerial/buried	Wall/trim	Wall/trim or conduit	Wall with Clear Track ILU fiber pathway	Wall with Clear Track Quad fiber pathway	Wall with Clear Track Hallway fiber pathway	
Indoor/Outdoor	Indoor/outdoor	Indoor/outdoor riser, indoor riser, indoor plenum	Indoor/outdoor	Indoor only	Indoor only	Indoor only	
Fiber Count	1	1-2	1	1	1-4	8, 12 and 16	
Fiber Type	Ultra bend-insensitive single-mode fiber	Ultra bend-insensitive or single-mode fiber	Ultra bend-insensitive or single-mode fiber	Ultra bend-insensitive fiber	Ultra bend-insensitive fiber	Ultra bend-insensitive fiber	
Option to Preconnectorize	Yes	Yes	Yes	No	No	Yes	
Packaging	Bulk	Bulk or reel in a box	Bulk or reel in a box	Spool in a box	Spool in a box	Spool in a box	
Quick Facts	<ul> <li>Enhanced jetting, push-and-pull performance</li> <li>Eliminates indoor ONT transitions with a flame-rated indoor subunit</li> </ul>	<ul> <li>Self-bend-limiting jacket allows for widest variation of installation methods including stapling</li> <li>Large color selection</li> </ul>	Optimized for running inconspicuously under carpet and along door frames or molding Suitable for raceway and microduct installations Large color selection	<ul> <li>Adhesive tape on the back of the pathway enables fast-and-easy installation on practically any surface</li> <li>Optional cover provides additional durability with virtual invisibility</li> </ul>	Use with Clear Track Micro Point-of-Entry (POE) wall cover for home run drops or for use with Hallway Small POE     Optional cover provides additional durability with virtual invisibility	Use with the Clear Track Hallway small POE box to terminate a field-mounted mechanical connector and test access point or splice to the living unit     Optional cover provides additional durability with virtual invisibility	

Corning Optical Communications < 🕏 > FTTP Selection Guide | CRR-630-AEN | Page 43



## Field-Installable Connectors

Field connectorization is fast and convenient whether you're looking for a fusion or mechanical splice. Corning offers both indoor and outdoor solutions in a variety of connector types and toolkits to support your application of choice. With high-optical performance of factory-polished connectors and immediate feedback on the quality of the connector installation, you can be assured of reliable connections. Evaluate the connectorization option that best suits your deployment and take advantage of the craft-friendly products throughout this section.

### **Mechanical Connectors and Splices** Other CORNING 11111 No Polish Connector + Corning® Fibrlok® OptiTap® Field-FuseLite II Splice On Corning<sup>®</sup> OptiSnap® Connectors Installable Connectors (NPC+) (NPC) Optical Fiber Splice 2529 Single-mode/ Single-mode/ Single-mode/ Single-mode/ Single-mode/ **Fiber Compatibility** Single-mode Single-mode multimode multimode multimode multimode multimode 250, 900 µm fibers 250, 900 µm fibers 250, 900 µm fibers 250, 900 µm fibers **Cable Compatibility** 1.6, 2.0, 3.0, or 4.8 mm 250, 900 µm fibers ROC™ drop 900 cable 250, 900 µm fibers 1.6. 2.0. 2.9 mm cables 1.6, 2.0, 3.0 mm cables 1.6. 2.0. 2.9 mm cables cables **Fiber Subunit Compatibility** 900, 250 μm 900, 250 μm 900 μm 900, 250 μm 900, 250 μm 900, 250 μm 900, 250 μm Indoor/outdoor in Indoor/outdoor in Indoor/outdoor in Indoor/outdoor in Indoor/outdoor in Indoor/outdoor in **Environment** appropriate hardware Outdoor appropriate hardware appropriate hardware appropriate hardware appropriate hardware appropriate hardware or enclosures and enclosures or enclosures or enclosures or enclosures or enclosures SC APC, SC UPC, LC SC APC, SC UPC, OptiSnap SC APC SC APC, SC UPC, APC, LC UPC, ST® connector as LC APC, LC UPC, LC APC, LC UPC, **Connector Style** SC UPC, SC APC N/A SC APC. SC UPC foundation with compatible ST compatible ST compatible, MTP® PRO connectors hardened OptiTap kit connectors connectors 80611622145 Compatible fusion (APC Installation Kit) **Toolkit Required** 80610581870 TKT-FIOT-ROC-CF TKT-FIOT-ROC TKT-NPCP-FBC007 80611323793 splicer with 80611622459 appropriate handler (UPC Installation Kit) Individual connectors Individual connectors Convenience pack of Convenience pack Convenience pack Convenience pack of Convenience pack **Packaging** or convenience pack or convenience pack 48 pieces in 6 piece of 60 of 60 6 or 25 connectors of 60 of 25 of 25 sub-packs No installation tool Designed for rapid Suited for adds/ Excellent back Ideal for drops of required, designed High-quality field terminations at moves/changes or odd lengths, for all skill levels. Low cost of tooling, reflection splice without the large-volume the home in FTTH **Quick Facts** inventory excellent optical ideal for all FTTx performance applications or in need for a termination installations reduction, or and mechanical in outdoor fusion splicer the central office/ projects in the emergency repairs performance for environments



FTTx applications

headend

central office



As 5G wireless services proliferate, operators are choosing a variety of methods to accomplish these deployments. By leveraging shorter distance and longer reach wavelengths, radio heads and antennas are popping up in a myriad of locations from rooftops to street lamps and water towers, too. One thing is for certain, these systems will require fiber to backhaul the traffic generated. If you're looking to support a combination of services on your network over time, we've got the experience and solutions to help you build one network to manage it all.

		xWDM Components		LC UPC Connectors			
CORNING			A				
	xWDM device	CRAN Centrix™ Cassette	DWDM Multiport Terminal	LC Simplex Assembly	LC Duplex Assembly	LC Multifiber Assembly	
Environment	Mobile switch center, CRAN hut or outside plant			Radio head or consolidation point			
Purpose	Combines multiple wavelength signals to optimize fiber utilization			Provides optical connectivity to macro and small cell devices			
Туре	Available in CWDM or DWDM configurations as requested			<ul> <li>Simplex or Duplex</li> <li>Various protective shrouds for compatibility with active electronics providers</li> </ul>			
Quick Facts	Even in dedicated CPRI send/receive duplex systems, overlaying FTTH with wireless signals require coexistence xWDM devices			Although there are many options, most radios utilize standard LCs as the key component for connectivity			

xWDM devices and LC connectors are key enabling components that allow for convergence of an existing FTTP network with wireless capability. The fundamental infrastructure components otherwise remain the same and can be found elsewhere in this guide.

In particular, look for solutions that help in congested areas, such as:

- MiniXtend® cables for microduct applications
- Evolv<sup>™</sup> terminals for discrete placement
- FlexNAP<sup>™</sup> Systems to create plug and play access points







## **LETS CONNECT!**







CO/HE Solutions www.corning.com/isp

Hybrid Fiber Coax Solutions www.corning.com/mso

Community Broadband Solutions www.corning.com/community-broadband

FTTH Solutions www.corning.com/ftth

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC 28216 USA • 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2018, 2023 Corning Optical Communications. All rights reserved. CRR-630-AEN / April 2023



