


CORNING

MiniXtend[®] Cables with Binderless^{*} FastAccess[®] Technology

Smaller Cables, Bigger Possibilities[†]


Faster



Up to **70% faster** cable access
Up to **80% lower** installation costs




Lighter




Up to **70% lighter** with improved cable handling

Reduced Risk




Craft-friendly cable prep

Improved Density



50% smaller than loose tube cables

Future Ready



Easier installations

* Corning's patented Binderless FastAccess[®] Technology refers to the combination of a Corning FastAccess Technology jacket with an innovative technology used to bind cable construction through the manufacturing process, eliminating the use of binder yarns and waterblocking tapes.

† When compared to traditional loose tube cable