

PREMIUM Certificate

no. z3300j-13-E

Customer:

Corning Optical Communications GmbH & Co. KG
Leipziger Str. 121
10117 Berlin, Germany

VALID TO APRIL 2018

Test sample(s):

Mating Adapter:

Adapter LC

Duplex, composite housing, ceramic insert

Part-no.: ADP-DLCO-CCNRF-CLS (SM)
ADP-DLCO-CCBRF-CLS (MM black housing)
ADP-DLCO-CCKRF-CLS (MM beige housing)

SM = singlemode; MM = multimode

Applied standard(s):

GHMT PVP Testplan-optical fibre Ed-2.0 (2013-03)

Result(s):

The sample meets the limits of the specified standards and regulations with respect to the parameters indicated above.

Mating Adapter, optical fibre

GHMT PREMIUM Verification Program, GHMT PVP

Ongoing compliance with the specifications is monitored within the framework of regular sampling, which cannot be influenced by the customer, thus defining high standards as regards continuous manufacturing quality.

This Certificate refers to the comprehensive test report no. P3300j-13-D and shall only be applicable in conjunction with the test report.

Bexbach, 06. October 2017



Dirk Wilhelm, engineer
(Chairman of the Managing Board)



GHMT AG

In der Kolling 13
66450 Bexbach / Germany

PO box11 16
66442 Bexbach / Germany

T: +49 6826 92 28-0
F: +49 6826 92 28-290

info@ghmt.de
www.ghmt.de

Test laboratory accredited by DAkkS in accordance with DIN EN ISO/IEC 17025.
The accreditation is valid for the test methods listed in certificate D-PL-17559-01-00.

RELIABILITY IN TOTAL
REQUIRES ACCURACY IN DETAIL.