

EDGE8™ Adapter Panels, MTP®

16F, RPS, 2 port panel with 2 aqua adapters

CORNING

EDGE8 40G patch cords allow for the seamless migration to higher data rates.

Features and Benefits

Installation

Can be installed or removed from the front or rear of a housing

Key identifiers

Gray color for easy identification as a Base-8 component

Network upgrades

Facilitate in easy-open containers

32-fiber Panel

Provide MTP connection points between trunks and harness or extender trunks

12 color-coded mechanical key positions

Prevents mismatch of networks

Keyed and non-keyed connectors and adapters


Provide security in network panel

Adapter options

Adapters are colored to provide network segmentation

16F Panel

Provides MTP connection points between trunks and harnesses or extender trunks



Specifications

General Specifications	
Application	Data Center
Product Type	Panels
Fiber Category	50 µm MM (OM3/OM4/OM5)

Design - Hardware	
Adapter Color Back	Aqua
Adapter Color Front	Aqua
Adapter Type Back	MTP®
Number of MTP Ports	2
Fiber Count	16

EDGE8™ Adapter Panels, MTP®

16F, RPS, 2 port panel with 2 aqua adapters



Mechanical Characteristics

Dimensions (W x D x H)	60.9 mm x 125.9 mm x 11.8 mm (2.4 in x 4.96 in x 0.46 in)
------------------------	---

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Ordering Information

Part Number	EDGE8-CP16-V3
Product Description	EDGE8™ Adapter Panel, MTP®, 16F, RPS, 2 port panel with 2 aqua adapters
EAN Code	4056418139586

Shipping Information

Packing dimensions (L x W x H)	178 mm x 121 mm x 19 mm (7.0 in x 4.75 in x 0.75 in)
Shipping Weight	0.2 kg (0.4 lb)
Units per Delivery	1/1



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2018 Corning Optical Communications. All rights reserved.

