

UniCam® High-Performance Installation Toolkit 2

CORNING

The UniCam® high-performance toolkit 2 was developed to reduce the amount of time required to terminate a single connector and to provide operational feedback and guidance throughout the termination process. Termination speeds are 25 percent faster by reducing the number of steps in the termination process. Installation of an LC, SC or ST® compatible connectors can be accomplished in 45 seconds with the UniCam high-performance toolkit 2 (TKT-UNICAM-PFC2). Every UniCam connector is guaranteed to meet the published performance specification at the time of installation. The UniCam high-performance installation tool 2 is also an intelligent tool that provides step-by-step guidance throughout the termination process, but is also capable of detecting missteps and providing guidance on how to correct them. Guidance is provided via an integrated LCD screen, featuring Corning's Gorilla Glass, using animated videos detailing the termination process. An additional 7-in LCD video panel is integrated into the kit providing guidance for other process steps such as fiber preparation, cleaving and maintenance. Connector loading is simplified courtesy of a new purple handler that ensures proper loading orientation and the transition between SC/ST to LC connectors is accomplished by simply rotating the VFL adapter either left or right. The new installation tool can be powered by two AA batteries or by a mini USB port located on the lid (cable included). The installation tool also notifies you when maintenance is needed, tells you how to perform maintenance, and when the tool is out of its operating temperature range.



Part Number: TKT-UNICAM-PFC2

Features and Benefits

45 percent fewer termination steps

Faster termination speeds

Two integrated LCD video panels

Step-by-step installation instructions

Operational feedback and corrective guidance

Fewer installation errors

Customizable features

Modify screen brightness, maintenance cycle duration, auto shut-off

UniCam Connector flat cleaver (FBC-007)

Simple operation and superior cleave quality

Remote software updates

Easily update tool software in the field

CORNING

UniCam® High-Performance Installation Toolkit 2



Specifications

General Specifications

| | |
|---------------|------------------------------|
| Product Type | Connector Tools and Toolkits |
| Technology | No-Epoxy/No-Polish |
| Compatibility | LC, SC and ST® compatible |

Mechanical Characteristics

| | |
|--------------------|--|
| Weight | 3.54 kg (7.8 lb) |
| Dimensions (HxWxD) | 10.8 cm x 38.7 cm x 30.5 cm (4.25 in x 15.25 in x 12 in) |

Chemical Characteristics

| | |
|------|---|
| RoHS | Free of hazardous substances according to RoHS 2011/65/EU |
|------|---|

Ordering Information

| | |
|---------------------|---|
| Part Number | TKT-UNICAM-PFC2 |
| Product Description | UniCam® high-performance toolkit 2: includes high-performance installation tool 2 for termination of multimode and single-mode LC, SC and ST® compatible connectors; includes high-performance precision flat cleaver, 7-in LCD video panel, and all required fiber preparation, cleaning tools and materials |

Shipping Information

| | |
|--------------------|--|
| Units per Delivery | 1/1 |
| Package Contents | UniCam® high-performance installation tool 2, precision flat fiber cleaver, crimp tool, 7-in LCD video panel, fiber preparation tools and fiber cleaning tools |
| Dimensions (HxWxD) | 17.8 cm x 48.3 cm x 35.6 cm (7 in x 19 in x 14 in) |
| Shipping Weight | 4.22 kg (9.3 lb) |



UniCam® High-Performance Installation Toolkit 2

The CORNING logo is a blue square with the word "CORNING" in white, uppercase, sans-serif font centered inside.

Notes



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks.

All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2018 Corning Optical Communications. All rights reserved.

The CORNING logo is the word "CORNING" in a large, black, all-caps, sans-serif font.